

CLARKE CDP 5DD Bench Drill



- Totally enclosed 230V fan cooled motor
- Precision engineered bearings, columns and tables
- Table tilts 0-90° to the left and right
- Easy to alter speed and belt tensions
- Extra large column support castings for strength and stability
- Safety cut-out on belt guard

Technical Data

Chuck Capacity	13mm
Spindle Taper	B16
Speeds	5
RPM	545-2530
Table Type	Square - Dry
Table Size	165 x 162mm
Motor	250W
Max. Distance - Chuck to Table	168mm
Max. Distance - Chuck to Base	260mm
Base Size	180 x 143mm
Overall Height	515mm
Weight	19kg