



■ Features :

- Universal AC input / Full range
- Built-in active PFC function
- Protections: Short circuit / Overload / Over voltage / Over temperature
- 5"x3" compact size
- Free air convection for 100W and 145W with 20.5 CFM forced air
- Medical safety approved (2 x MOPP between primary to secondary)
- With power good and fail signal output
- * No load power consumption under 0.75W by PS-ON control (G model)
- * Standby 5V@0.8A with fan, @0.6A without fan (G model)
- * Suitable for BF application with appropriate system consideration
- 3 years warranty

G: With 5Vsb & no load power consumption < 0.75 W Blank: Basic function (without 5Vsb)

RPT G - 160A









SPECIFICATION

MODEL		RPT□-160A			RPT□-160B			RPT□-160C			RPT□-160D			
	OUTPUT NUMBER	CH1	CH2	CH3	CH1	CH2	CH3	CH1	CH2	СНЗ	CH1	CH2	CH3	
ОИТРИТ	DC VOLTAGE	5V	12V	-5V	5V	12V	-12V	5V	15V	-15V	5V	12V	24V	
	RATED CURRENT (20.5CFM)	14A	5.5A	1A	14A	5A	1A	14A	3.6A	1A	11A	5A	1.2A	
	CURRENT RANGE (convection)	0.6 ~ 9A	0.2 ~ 3.8A	0.1 ~ 0.6A	0.6 ~ 9A	0.2 ~ 3.4A	0.1 ~ 0.8A	0.6 ~ 9A	0.1 ~ 2.6A	0.1 ~ 0.8A	0.3 ~ 8A	0.2 ~ 2.6A	0.15 ~ 1A	
	CURRENT RANGE (20.5CFM)	0.6 ~ 14A	0.2 ~ 5.5A	0.1 ~ 1A	0.6 ~ 14A	0.2 ~ 5A	0.1 ~ 1A	0.6 ~ 14A	0.1 ~ 3.6A	0.1 ~ 1A	0.3 ~ 11A	0.2 ~ 5A	0.15 ~ 1.2A	
	RATED POWER (convection) Note.7	98.6W			98.4W			99W			98.2W			
	RATED POWER (20.5CFM) Note.8	145W			146W			143W			147.8W			
	RIPPLE & NOISE (max.) Note.2	100mVp-p 120mVp-p 120mVp-p			100mVp-p 120mVp-p 120mVp-p			100mVp-p 150mVp-p 150mVp-p			100mVp-p 120mVp-p 200mVp-p			
	VOLTAGE ADJ. RANGE	CH1:5 ~ 5	CH1:5~5.5V								•			
	VOLTAGE TOLERANCE Note.3	±2.0%	±5.0%	-5,+7%	±2.0%	±5.0%	-4,+5%	±2.0%	±4.0%	±8.0%	±2.0%	±5.0%	+7,-5%	
	LINE REGULATION	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%	±1.0%	±0.5%	±1.0%	±1.0%	
	LOAD REGULATION	±1.5%	±3.0%	-5,+6%	±1.5%	±3.0%	-4,+5%	±2.0%	±3.0%	±8.0%	±1.5%	±3.0%	-3,+4%	
	SETUP, RISE TIME	1800ms, 3	1800ms, 30ms/230VAC 3500ms, 30ms/115VAC at full load											
	HOLD UP TIME (Typ.)	16ms/230VAC/115VAC at full load												
INPUT	VOLTAGE RANGE Note.6	90 ~ 264VAC 127 ~ 370VDC												
	FREQUENCY RANGE	47 ~ 63Hz												
	POWER FACTOR (Typ.)	PF>0.93/2	PF>0.93/230VAC											
	EFFICIENCY (Typ.)	84%												
	AC CURRENT (Typ.)	1.8A/115VAC 0.9A/230VAC												
	INRUSH CURRENT (Typ.)	COLD START 35A/115VAC 70A/230VAC												
	LEAKAGE CURRENT Note.9	Earth leakage current < 200μA/264VAC, Touch current < 100μA/264VAC												
PROTECTION		105 ~ 135% rated output power												
	OVERLOAD	Protection type: Hiccup mode, recovers automatically after fault condition is removed												
		CH1: 5.75 ~ 6.75V												
	OVER VOLTAGE	Protection type : Shut down o/p voltage, re-power on to recover												
	OVER TEMPERATURE	TSW1: Shut down o/p voltage, recovers automatically after temperature goes down												
		TSW2: Shut down o/p voltage, re-power on to recover												
	5V STANDBY (G model)	5VSB:5V@0.6A without fan, 0.8A with fan 20.5CFM; tolerance ± 2%, ripple:50mVp-p(max.)												
FUNCTION	PS-ON INPUT SIGNAL (G model)	Power on: PS-ON = "Hi" or " > 2 ~ 5V"; Power off: PS-ON = "Low" or " < 0 ~ 0.5V"												
	POWER GOOD / POWER FAIL	500ms>P	500ms>PG>10ms											
ENVIRONMENT	WORKING TEMP.	-20 ~ +70	-20 ~ +70°C (Refer to "Derating Curve")											
	WORKING HUMIDITY	20 ~ 90% RH non-condensing												
	STORAGE TEMP., HUMIDITY	-40 ~ +85	-40 ~ +85°C, 10 ~ 95% RH											
	TEMP. COEFFICIENT	±0.03%/°C (0~50°C)												
	VIBRATION	10 ~ 500Hz, 2G 10min./1cycle, 60min. each along X, Y, Z axes												
SAFETY & EMC (Note 4)	SAFETY STANDARDS	ANSI/AAN	ANSI/AAMI ES60601-1, TUV EN60601-1 approved											
	ISOLATION LEVEL	Primary-S	Primary-Secondary: 2xMOPP, Primary-Earth:1xMOPP, Secondary-Earth:1xMOPP											
	WITHSTAND VOLTAGE	I/P-O/P:4	I/P-O/P:4KVAC I/P-FG:2KVAC O/P-FG:1.5KVAC											
	ISOLATION RESISTANCE	I/P-O/P, I/	P-FG, O/P-	FG:100M (Ohms / 500\	/DC / 25°C	/ 70% RH							
	EMC EMISSION	Complian	Compliance to EN55011 (CISPR11), EN55022 (CISPR22) Class B, EN61000-3-2,-3											
	EMC IMMUNITY	Complian	Compliance to EN61000-4-2,3,4,5,6,8,11, EN55024, EN60601-1-2, EN61204-3, medical level, criteria A											
OTHERS	MTBF	191.4K hr	191.4K hrs min. MIL-HDBK-217F (25°C)											
	DIMENSION	127*76.2*	34.6mm (L	*W*H)	` '									
	PACKING	0.33Kg; 3	6pcs/12.9K	g/0.79CUF	Т									
	1 All parameters NOT enecia				201/40 :==			°C -4		-4				

NOTE

- 1. All parameters NOT specially mentioned are measured at 230VAC input, rated load and 25°C of ambient temperature.
- 2. Ripple & noise are measured at 20MHz of bandwidth by using a 12" twisted pair-wire terminated with a 0.1 uf & 47uf parallel capacitor.

 3. Tolerance: includes set up tolerance, line regulation and load regulation.

 4. The power supply is considered a component which will be installed into a final equipment. All the EMC tests are been executed by mounting the unit on
- a 360mm*360mm metal plate with 1mm of thickness. The final equipment must be re-confirmed that it still meets EMC directives. For guidance on how to perform these EMC tests, please refer to "EMI testing of component power supplies." (as available on http://www.meanwell.com)
- 5. HS1,HS2 & HS3 can not be shorted.
- 6. Derating may be needed under low input voltages. Please check the derating curve for more details.
- 7. The rated power includes 5Vsb @ 0.6A. 8. The rated power includes 5Vsb @ 0.8A.
- Touch current was measured from primary input to DC output.



