Product data sheet Characteristics

BMXCPS2000

power supply module X80 - 100..240 V AC - 20 W





Range of product	Modicon X80		
Product or component type	Power supply module		
Product compatibility	Not compatible with BMEXBP02	Not compatible with BMEXBP02	
Primary voltage	100240 V		
Supply circuit type	AC		
Secondary power	10.8 W 24 V DC sensor power supply 16.8 W 24 V DC I/O module power supply and processor		
	8.3 W 3.3 V DC I/O module logic power supply		

Complementary

Primary voltage limit	85264 V	
Network frequency	50/60 Hz	
Network frequency limits	4763 Hz	
Apparent power	0.07 kVA	
Input current	0.31 A 240 V	
	0.61 A 115 V	-
Inrush current	<= 30 A 120 V	. <u>v</u>
	<= 60 A 240 V	,
I²t on activation	<= 12 A ² .s 240 V	<u></u>
It on activation	<= 0.03 A.s 120 V	
	<= 0.06 A.s 240 V	⊽ α
Protection type	Internal fuse not accessible primary circuit	
	Overload protection secondary circuit	9
	Overvoltage protection secondary circuit	ri de
	Short-circuit protection secondary circuit	ta
Current at secondary voltage	0.45 A 24 V DC sensor power supply	
	0.7 A 24 V DC I/O module power supply and processor	<u> </u>
	2.5 A 3.3 V DC I/O module logic power supply	
Power dissipation in W	<= 8.5 W	
Status LED	1 LED green rack voltage OK	
	1 LED green sensor voltage	e e
Control type	RESET push-button cold restart	. <u>.</u> <u>n</u> C

Electrical connection	1 connector 2 pin(s) alarm relay 1 connector 5 pin(s) line supply, protective earth, 24 V DC input sensor
Insulation resistance	>= 100 MOhm primary/ground >= 100 MOhm primary/secondary
Product weight	0.3 kg

Environment

Immunity to microbreaks	<= 1 ms	
Dielectric strength	1500 V primary/ground 1500 V primary/secondary I/O module logic power supply 1500 V primary/secondary I/O module power supply and processor 2300 V primary/secondary sensor power supply 500 V 24 V sensor output/ground	
Vibration resistance	3 gn	
Shock resistance	30 gn	
IP degree of protection	IP20	
Product certifications	CSA UL Merchant Navy CE EAC RCM	
Standards	EN/IEC 61010-2-201 UL 61010-2-201 CSA C22.2 No 61010-2-201 EN/IEC 61131-2	
Ambient air temperature for storage	-4085 °C	
Ambient air temperature for operation	060 °C	
Relative humidity	595 % without condensation 55 °C	
Protective treatment	TC	
Operating altitude	02000 m 20005000 m (with derating factor)	

Offer Sustainability

Sustainable offer status	Green Premium product	
RoHS (date code: YYWW)	Compliant - since 0722 - Schneider Electric declaration of conformity	
	Schneider Electric declaration of conformity	
REACh	Reference not containing SVHC above the threshold	
	Reference not containing SVHC above the threshold	
Product environmental profile	Available	
	End of life manual	
Product end of life instructions	Available	

Contractual warranty


Warranty period	18 months	

Product data sheet **Dimensions Drawings**

BMXCPS2000

Modules Mounted on Racks

Dimensions




- (1) With removable terminal block (cage, screw or spring).
- With FCN connector.
- (2) On AM1 ED rail: 35 mm wide, 15 mm deep. Only possible with BMXXBP0400/0400H/0600/0600H/0800/0800H rack.

Rack references	a in mm	a in in.
BMXXBP0400 and BMXXBP0400H	242.4	09.54
BMXXBP0600 and BMXXBP0600H	307.6	12.11
BMXXBP0800 and BMXXBP0800H	372.8	14.68
BMXXBP1200 and BMXXBP1200H	503.2	19.81

BMXCPS2000


Connection of Alternating Current Power Supply Modules

Connection of a PLC Station Constituted of a Single Rack



- Q General isolator
- KM Line contactor or circuit breaker
- (1) Insulation connector bar for locating grounding errors
- (2) Available current of 0.45 A for the BMXCPS2000 module or 0.9 A for the BMXCPS3500 module

Connection of a PLC Station Constituted of Several Racks



- Q General isolator
- KM Line contactor or circuit breaker
- (1) Insulation connector bar for locating grounding errors
- (2) Available current of 0.45 A for the BMXCPS2000 module or 0.9 A for the BMXCPS3500 module