

ZBVB8

yellow light block for head Ø22 integral LED 24V
screw clamp terminals



Main

| | |
|-------------------------------|--|
| Range of product | Harmony XB4 Harmony XB5 |
| Product or component type | Light block |
| Device short name | ZBV |
| Sale per indivisible quantity | 5 |
| Connections - terminals | Screw clamp terminals : $\leq 2 \times 1.5 \text{ mm}^2$ with cable end conforming to EN 60947-1 Screw clamp terminals : $\geq 1 \times 0.22 \text{ mm}^2$ without cable end conforming to EN 60947-1 |
| Signalling type | Steady |
| Light source | Protected LED |
| Bulb base | Integral LED |
| Light block supply | Direct |
| Light source colour | Yellow |
| [Us] rated supply voltage | 24 V AC/DC, 50/60 Hz |

Complementary

| | |
|-----------------------------|---|
| Product weight | 0.017 kg |
| Tightening torque | 0.8...1.2 N.m conforming to EN 60947-1 |
| Shape of screw head | Cross head compatible with Philips no 1 screwdriver Cross head compatible with pozidriv No 1 screwdriver Slotted head compatible with flat Ø 4 mm screwdriver Slotted head compatible with flat Ø 5.5 mm screwdriver |
| Supply voltage limits | 19.2...30 V DC 21.6...26.4 V AC |
| Current consumption | 18 mA |
| Service life | 100000 h at rated voltage and 25 °C |
| Surge withstand | 1 kV conforming to IEC 61000-4-5 |
| Mounting of block | Front mounting |
| Electrical composition code | M1 M2 M3 |

M4
M5
M6
M10
MF1
P1
P2

| | |
|--------------------|-----|
| Compatibility code | ZBV |
|--------------------|-----|

Environment

| | |
|----------------------|----|
| Protective treatment | TH |
|----------------------|----|

| | |
|-------------------------------------|-------------|
| Ambient air temperature for storage | -40...70 °C |
|-------------------------------------|-------------|

| | |
|---------------------------------------|-------------|
| Ambient air temperature for operation | -40...70 °C |
|---------------------------------------|-------------|

| | |
|-------------------------|------------------------------|
| IP degree of protection | IP20 conforming to IEC 60529 |
|-------------------------|------------------------------|

| | |
|-----------|---|
| Standards | EN/IEC 60947-5-1 JIS C 4520 UL 508 EN/IEC 60947-5-5 CSA C22.2 No 14 EN/IEC 60947-1 EN/IEC 60947-5-4 |
|-----------|---|

| | |
|------------------------|------------------|
| Product certifications | UL listed CSA |
|------------------------|------------------|

| | |
|-------------------------------|----------------------------------|
| Resistance to fast transients | 2 kV conforming to IEC 61000-4-4 |
|-------------------------------|----------------------------------|


| | |
|--------------------------------------|------------------------------------|
| Resistance to electromagnetic fields | 10 V/m conforming to IEC 61000-4-3 |
|--------------------------------------|------------------------------------|

| | |
|---------------------------------------|--|
| Resistance to electrostatic discharge | 6 kV on contact (on metal parts) conforming to IEC 61000-4-2 8 kV in free air (in insulating parts) conforming to IEC 61000-4-2 |
|---------------------------------------|--|

| | |
|--------------------------|---------------------------------|
| Electromagnetic emission | Class B conforming to IEC 55011 |
|--------------------------|---------------------------------|

Dimensions

with ZB5AZ009 Fixing Collar



with ZB4BZ009 Fixing Collar

