



Platinum Resistance Pt1000 Class B Sensor with Teflon[®] insulated lead



About Labfacility

Formed in 1971, Labfacility specialize in the field of Temperature and Process Measurement.

We are the largest UK manufacturer of both temperature sensors and thermocouple connectors.

Quality & Service

Quality and Service are key elements in the continued growth of Labfacility.

Technical support is always freely available from our experienced technical sales teams and the company has ISO9001 accreditation.

- Pt1000 element to IEC 751 Class B
- 2 wire configuration
- Temperature range -50°C to + 200°C
- Pt1000 element in a 4.0mm diameter 316 stainless steel probe
- 1 metre Teflon[®] insulated twisted lead, 2 core
- Specifications

Sensor type:	Pt1000 (1000 Ohms @ 0°C) to IEC 751, Class B
Construction:	Insulated element in a 4.0mm diameter 316 stainless steel probe
Probe temperature range:	-50°C to +200°C
Extension cable:	1 metre Teflon [®] insulated 2 core twisted leads
Termination:	2-wire tails

Probe dimensions (dia. x length)	Product code	Order code
4mm x 40mm	RAA-S2B-4.0-40-NP-1.0-C5-T-PT1000	XF-1142-FAR

Contact Details

Email
sales@labfacility.com

Website
www.labfacility.com