



Purchase

APC
 PMM30

Overview

Description	Power Management Modules (PMMs) offer a proven solution for panel-based room distribution of power. With up to 252 poles and a 200%-rated neutral bus, the PMM is ideally suited to provide reliable power to the equipment in data centers of all sizes, from small to very large. Spacious input and output cable access and bottom cable entry simplify the setup process, and hinged panels provide convenient front access to the PMM. Easily expand the PMM configuration by adding Remote Power Management Modules. The PMM is custom-configurable to meet the needs of unique installation sites and is factory-assembled for quality assurance. With these features, the PMM a highly reliable and adaptable distribution system.
Model Name	MGE Power Management Module 30 kVA
Includes	Installation guide , User Manual
Standard Lead Time	Special Order - Call for Quoted Lead Times
Product Distribution	Antigua And Barbuda , Anguilla , Netherlands Antilles , Argentina , Aruba , Barbados , Bermuda , Bolivia , Brazil , Bahamas , Belize , Canada , Chile , Colombia , Costa Rica , Cuba , Dominica , Dominican Republic , Ecuador , Falkland Islands (Malvinas) , Grenada , Guadeloupe , Guatemala , Guyana , Honduras , Haiti , Jamaica , SAINT KITTS AND NEVIS , Cayman Islands , SAINT LUCIA , Martinique , Mexico , Nicaragua , Panama , Peru , Puerto Rico , Paraguay , El Salvador , Turks And Caicos Islands , Trinidad And Tobago , United States , Uruguay , SAINT VINCENT AND THE GRENADINES , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Nominal Output Voltage	120V , 208V 3PH
Maximum Total Current Draw per Phase	83 A

Input

Nominal Input Voltage	120V , 208V 3PH , 480V 3PH
Input Frequency	60 Hz +/- 5 Hz
Input Connections	Hard Wire 4-wire (3PH + G) , Hard Wire 5-wire (3PH + N + G)
Maximum Line Current per phase	83 A

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

Physical

Net Weight	488.64 kg
Maximum Height	1833 mm
Maximum Width	1080 mm
Maximum Depth	752 mm
Shipping Weight	488.64 kg
Shipping Height	1833 mm
Shipping Width	1080 mm
Shipping Depth	752 mm
Color	Beige


Environmental

Operating Environment	-10 - 40 °C
Operating Relative Humidity	10 - 90 %
Operating Elevation	0-999.9 meters
Storage Temperature	-40 - 60 °C
Storage Relative Humidity	10 - 90 %
Storage Elevation	0-9000 meters

Conformance

Approvals	CSA C22.2 No. 60950 , FCC Part 15 Class A , UL 60950
Standard warranty	1 year repair or replace


Dimensions



a		b		b1 (1)		P1 (2)	
mm	in.	mm	in.	mm	in.	mm	in.
132	5.19	74	3	104	4.09	78	3.07

- (1) With fixing clips (included with product)
 (2) P1: depth with RJ45 cable XBTZ9780 (for Twido, TSX Micro and Premium)

Cut-out for Flush Mounting



Panel thickness = 1.5...6 mm / 0.05...0.23 in.

H		G		r max.	
±0.4 mm	±0.02 in.	±0.5 mm	±0.02 in.	mm	in.
63	2.48	119.4	5	1.5	0.05