



Share:



### SC620I

Average Customer Review ★★★★☆ 3

1 of 2 (50%) reviewers would recommend this product to a friend.

[Read all reviews](#) | [Write a review](#)

Share this Product: [Facebook](#) [Twitter](#) [LinkedIn](#) [Email](#)



Description: APC Smart-UPS SC is ideal for small and medium businesses looking to protect networking equipment and point-of-sale (POS) devices from power disturbances and outages. The Smart-UPS SC features network grade protection, hot swap batteries, and built-in data line protection for worry free uninterruptible power protection for increased availability. Built on the same standards as the award-winning Smart-UPS, Smart-UPS SC provides the basic features and manageability needed to protect entry-level applications

Includes : CD with software , Smart UPS signalling RS-232 cable , User Manual

- Product Overview
- Technical Specifications
- Documentation
- Software & Firmware
- Options
- Ratings & Reviews

#### Output

[Print Technical Specification](#)

Output power capacity	390Watts / 620VA
Max Configurable Power (Watts)	390Watts / 620VA
Nominal Output Voltage	230V
Output Frequency (sync to mains)	50/60Hz +/- 3 Hz
Topology	Line Interactive
Waveform type	Stepped approximation to a sinewave

Output Connections  
 (2) IEC Jumpers (Battery Backup)  
 (1) IEC 320 C13 (selector\_surgetitle)  
 (3) IEC 320 C13 (Battery Backup)

Transfer Time	2ms typical
---------------	-------------

#### Input

Nominal Input Voltage	230V
Input frequency	50/60 Hz +/- 3 Hz (auto sensing)
Input Connections	IEC-320-C14 inlet
Input voltage range for main operations	195 - 265V

#### Batteries & Runtime

Battery type	Maintenance-free sealed Lead-Acid battery with suspended electrolyte : leakproof	
Typical recharge time	5hour(s)	
Replacement Battery	RBC4	
Expected Battery Life (years)	3 - 5	
RBC Quantity	1	
Runtime	<a href="#">View Runtime Graph</a>	<a href="#">View Runtime Chart</a>
Efficiency	<a href="#">View Efficiency Graph</a>	

#### Communications & Management

Interface Port(s)	DB-9 RS-232
Control panel	LED status display with On Line : On Battery : Replace Battery and Overload indicators
Audible Alarm	Alarm when on battery : distinctive low battery alarm : overload continuous tone alarm
Emergency Power Off (EPO)	N/A

#### Surge Protection and Filtering

Surge energy rating	320Joules
Data Line Protection	RJ-45 Modem/Fax/DSL/10-100 Base-T protection
Filtering	Full time multi-pole noise filtering : 0.7% IEEE surge let-through : zero clamping response time : meets UL 1449

#### Physical

Maximum Height	6.6inches ( 168mm , 16.8CM )
Maximum Width	4.7inches ( 119mm , 11.9CM )
Maximum Depth	14.76inches ( 375mm , 37.5CM )
Net Weight	27.0lbs. ( 12.27KG )
Shipping weight	29.0lbs. ( 13.18KG )
Shipping Height	12.5inches ( 318mm , 31.8CM )
Shipping Width	10.3inches ( 262mm , 26.2CM )
Shipping Depth	20.0inches ( 508mm , 50.8CM )
Color	Grey

Operating Elevation	0-10000ft ( 0-3000meters )
Storage Temperature	-15 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000ft ( 0-15000meters )
Audible noise at 1 meter from surface of unit	45.0dBA
Online thermal dissipation	70.0BTU/hr
<b>Conformance</b>	
Approvals	CE, GOST, VCCI, VDE
Standard warranty	2 years repair or replace
<b>Sustainable Offer Status</b>	
RoHS	Compliant
REACH	REACH: Contains No SVHCs
PEP	Available in Documentation tab
EOL	Available in Documentation tab
Other Environmental Compliance	China RoHS



Sign up to stay up to date with best practices, new solutions and special offers.

Email

I am a...



OK

WHO WE ARE

- APC History
- Investor Relations
- Careers
- Sustainability

CONNECT WITH US

- Press
- APC Blog
- Schneider Electric TV
- Schneider Electric Data Center Blog
- Contact Us
- Rate this website

FIND A RESELLER

Zip/Postal Code    FIND

CATALOG KEYCODE

Enter Key Code    GO

TERMS & CONDITIONS | PRIVACY STATEMENT

© 2018, APC by Schneider Electric

