

## Product information

# 10.8V Rotary Hammer 14MM CXT



Satisfying the professional's needs

## HR140DZ

Battery Type	Lithium-ion
Voltage	10.8 v
Impact energy	1.0 J
Capacity in Concrete	14 mm
Capacity in Steel	10 mm
Capacity in Wood	13 mm
Impacts per minute	0 - 4900 ipm
Vibration K factor	1.5 m/sec <sup>2</sup>
Net weight	2.6 kg
No Load Speed	0 - 850 rpm
Vibration: Hammer Drilling	6.5 m/sec <sup>2</sup>
Noise sound pressure	84 dB(A)
Noise K factor	3 dB(A)
Noise sound power	95 dB(A)
Body only machine	1
Vibration: Drilling into metal	3.0 m/sec <sup>2</sup>



**STANDARD EQUIPMENT:** Side handle, Depth stop

- 2-mode operation: Rotary only and Rotary hammer
- Variable speed control by trigger
- Forward/reverse rotation
- LED job light
- One touch sliding chuck for easy bit installation and removal.
- Compact and lightweight design
- Vibration absorbing housing.

Details correct as of: 9-1-2018

Makita reserve the right to change specifications at any time owing to their policy of constant improvement.

Accessories shown are not necessarily supplied.

[www.makita.com](http://www.makita.com)