

Product availability : Stock - Normally stocked in distribution facility



### Main

Product or component type	Combination Starter
Range of product	S
Control circuit	Separate control circuit

### Complementary

[Uc] control circuit voltage	110 V AC 50 Hz 120 V AC 60 Hz
Motor starter type	Non reversing
Poles description	3P
Motor power hp	10 hp 460 V AC 3 phases 10 hp 575 V AC 3 phases
System Voltage	600 V AC
Control type	No control units
Local signalling	No indicator
Auxiliary contact composition	Without
Thermal overload type	Melting alloy 3 Thermal Units
Disconnecter device type	Fusible disconnect switch, Type H Fuse, 30 A
NEMA size	1

### Environment

NEMA degree of protection	NEMA 1 painted sheet steel and with external reset
---------------------------	--

### Ordering and shipping details

Category	21213 - 8538,39 SC,SD(NOT S*R,T,W)
Discount Schedule	CP1
GTIN	00785901748359
Nbr. of units in pkg.	1

Package weight(Lbs)	34.700000000000003
Returnability	Y
Country of origin	MX

**Offer Sustainability**

Sustainable offer status	Not Green Premium product
RoHS (date code: YYWW)	Will be compliant on 3Q2014 Will be compliant on 3Q2014
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold

**Contractual warranty**

Warranty period	18 months
-----------------	-----------