


SOLDER TERMINALS - CERAMIC INSULATED, FEEDTHROUGH, THREAD MOUNT



Dimensions in inches (mm)

How to order code

570 - XXXX - 01 - XX - 00

Basic Part No.

Terminal Finish


Material Code Table		
Component	Material	RoHS
Mounting Hex Nut	Brass	✓
Internal Tooth Lockwasher	Phosphor Bronze	✓
Insulator	Ceramic	✓
Mounting Stud	Brass	✓
Terminal	Brass	✓

Finish Code Table					
Dash No.	Terminal Finish	Mtg. Stud Finish	Mtg. Hex Nut Finish	Lock Washer Finish	RoHS
-01	Silver	Nickel	Nickel	Nickel	✓
-05	Electro-Solder	Nickel	Nickel	Nickel	X

Basic Part No.	A	B Max.	C	D	D1	D2	D3	D4	E	F
570-2012 -01	1.307 (33.20)	.559 (14.20)	.375 (9.53)	.500 (12.70)	.080 (2.03)	.050 (1.27)	.080 (2.03)	.050 (1.27)	.285 (7.24)	.282 (7.16)
570-1990 -01	.923 (23.44)	.383 (9.73)	.250 (6.35)	.375 (9.53)	.062 (1.57)	.043 (1.09)	.062 (1.57)	.043 (1.09)	.198 (5.03)	.184 (4.67)

Basic Part No.	G	H	J	K	L	T	IR (VRMS)
570-2012 -01	.093 (2.36)	.105 (2.67)	.093 (2.36)	.093 (2.36)	.062 (1.57)	3/8-32	3000
570-1990 -01	.046 (1.17)	.065 (1.65)	.054 (1.37)	.046 (1.17)	.050 (1.27)	1/4-28	2500

SOLDER TERMINALS - PTFE INSULATED, STAND OFF, THREAD MOUNT



Dimensions in inches (mm)

How to order code

570 - XXXX - XX - XX - 19

Basic Part No.

Insulator Colour
Terminal Finish

Material Code Table		
Component	Material	RoHS
Insulator	PTFE	✓
Mounting Stud	Brass	✓
Terminal	Brass	✓

Finish Code Table			
Dash No.	Terminal Finish	Mtg. Stud Finish	RoHS
-01	Silver	Cadmium	X
-05	Electro-Solder	Cadmium	X
-21	Silver	Nickel	✓

Insulation Colour Code Table	
Dash No.	Colour
-19	White

Fig.	Basic Part No.	L	A	B	C	D	D1	D2	D3	F	G	T	IR (VRMS)
1	570-1503 -01	.250 (6.35)	.500 (12.70)	.147 (3.73)	.128 (3.25)	.156 (3.96)	.066 (1.68)	.045 (1.14)	.125 (3.18)	.062 (1.57)	.031 (0.79)	4-40	3500
	570-1504 -01	.250 (6.35)	.640 (16.26)	.304 (7.72)	.180 (4.57)	.250 (6.35)	.140 (3.56)	.069 (1.75)	.245 (6.22)	.129 (3.28)	.100 (2.54)	6-32	3300
2	570-1510 -01	.100 (2.54)	.546 (13.87)	.147 (3.73)	.181 (4.60)	.156 (3.96)	.066 (1.68)	.045 (1.14)	.125 (3.18)	.062 (1.57)	.031 (0.79)	4-40	3500
	570-1511 -01	.156 (3.96)	.718 (18.24)	.304 (7.72)	.258 (6.55)	.250 (6.35)	.140 (3.56)	.069 (1.75)	.245 (6.22)	.129 (3.28)	.100 (2.54)	6-32	3300
3	570-1945 -01	.250 (6.35)	.334 (8.48)	.228 (5.79)	.062 (1.57)	.312 (7.92)	.093 (2.36)	.046 (1.17)	.250 (6.35)	.093 (2.36)	.063 (1.60)	6-32	5000
	-02	.375 (9.53)											
4	570-1947 -01	.125 (3.18)	.401 (10.19)	.228 (5.79)	.125 (3.18)	.312 (7.92)	.093 (2.36)	.046 (1.17)	.250 (6.35)	.093 (2.36)	.063 (1.60)	4-40	5000
	-02											6-32	