

WT 1012 + LC8076 - SOLDERING AND MAGNIFIER KIT



Soldering Stations

Power unit, 1 channel with soldering iron WSP 80 and safety rest WSR 201

Dimensions W x D x H (mm)	149 x 138 x 101
Dimensions W x D x H (Inch)	5.87 x 5.43 x 3.98
Weight (ca) in kg	1.9
Voltage	230 V, 50/60 Hz
Power output	95 W
Channels	1
Temperature range (depends on tool) °C	50 - 550
Temperature range (depends on tool) °F	150 - 950
Temperature accuracy °C	±9
Temperature accuracy °F	±17
Temperature stability °C	±2
Temperature stability °F	±4
Equipotential bonding	Via 3,5 mm pawl socket on front of device
Display	Backlit LCD
Air consumption l/min	---
Operating pressure	---
Capacity l/min	---
Vacuum	---

LC8076: Long Reach Slim Line Magnifier Lamp

Specifications: A round 16w daylight lamp with glass lens, featuring longer arms with sturdy joints for extra flexibility & positioning. Ideal for close-up intricate work.

Features & Benefits:

- Electronic ballast - more energy efficient
- 16 watt energy saving fluorescent tube (LC8076/T)
- Shadow free light with low heat emission
- Quality 125mm (5") lens, 3 dioptr (1.75x mag.)
- Removable sun protector cap
- Includes table clamp with cone holder for extra stability
- Cable length 1.5m