

PRODUCT FAMILY DATASHEET

PARATHOM SPECIAL T26

Special LED lamps for refrigerators



AREAS OF APPLICATION

- Small designer luminaires
- Domestic refrigerators
- Sewing machines
- Outdoor applications only in suitable luminaires

PRODUCT BENEFITS

- Low energy consumption
- Good all-around light emission
- Extremely small dimensions

PRODUCT FEATURES

- Mercury-free lamps





TECHNICAL DATA

Product description	Electrical data				Photometrical data				
	Nominal wattage	Nominal voltage	Max. lamp no. on circuit break. 10 A (B)	Max. lamp no. on circuit break. 16 A (B)	Nominal luminous flux	Rated luminous flux	Color temperature	Color rendering index Ra	Lumen main.fact.at end of nom.life time
P SPC.T26 12 1.3 W/827 E14 ¹⁾	1.30 W	220...240 V	500	800	110 lm	110 lm	2700 K	≥80	0.70
P SPC.T26 20 2.3 W/827 E14 ¹⁾	2.30 W	220...240 V			200 lm	200 lm	2700 K	80	0.70
P SPC.T26 20 2.3 W/865 E14 ¹⁾	2.30 W	220...240 V			200 lm	200 lm	6500 K	80	0.70

Product description	Light color (designation)	Light technical data	Dimensions & weight		Lifespan		Additional product data		
		Warm-up time (60 %)	Overall length	Diameter	Nominal lamp life time	Number of switching cycles	Base (standard designation)	Mercury content	Mercury-free
P SPC.T26 12 1.3 W/827 E14 ¹⁾	Warm White	< 0.50 s	63.0 mm	26.0 mm	8000 h	100000	E14	0.0 mg	Yes
P SPC.T26 20 2.3 W/827 E14 ¹⁾	Warm White	< 0.50 s	63.0 mm	25.0 mm	15000 h	100000	E14	0.0 mg	Yes
P SPC.T26 20 2.3 W/865 E14 ¹⁾	Cool Daylight	< 0.50 s	63.0 mm	25.0 mm	15000 h	100000	E14	0.0 mg	Yes

Product description	Capabilities	Certificates & standards	Country-specific categorizations
	Dimmable	Energy efficiency class	ILCOS
P SPC.T26 12 1.3 W/827 E14 ¹⁾	No	A++	DRBT/C-1,3/827-230-E14-26
P SPC.T26 20 2.3 W/827 E14 ¹⁾	No	A++	DRBT/F-2,2/827-230-E14-26
P SPC.T26 20 2.3 W/865 E14 ¹⁾	No	A++	DRBT/F-2,2/865-230-E14-26

¹⁾ All technical parameters apply to the entire lamp/Due to the complex production process for light-emitting diodes, the typical values shown for the technical LED parameters are purely statistical values that do not necessarily match the actual technical parameters of each individual product, which can vary from the typical value



P SPC.T26 12 1.3 W/827 E14

P SPC.T26 20 2.3 W/827 E14, P SPC.T26 20 2.3 W/865 E14

APPLICATION ADVICE

For more detailed application information and graphics please see product datasheet.

LOGISTICAL DATA

Product code	Product description	Packaging unit (Pieces/Unit)	Dimensions (length x width x height)	Volume	Gross weight
4058075042384	P SPC.T26 12 1.3 W/827 E14	Shipping carton box 20	150 mm x 122 mm x 77 mm	1.41 dm ³	278.00 g
4052899961289	P SPC.T26 20 2.3 W/827 E14	Shipping carton box 20	150 mm x 122 mm x 77 mm	1.41 dm ³	406.00 g
4052899961302	P SPC.T26 20 2.3 W/865 E14	Shipping carton box 20	150 mm x 122 mm x 77 mm	1.41 dm ³	406.00 g

The mentioned product code describes the smallest quantity unit which can be ordered. One shipping unit can contain one or more single products. When placing an order, for the quantity please enter single or multiples of a shipping unit.

REFERENCES / LINKS

For Guarantee see

- ▶ www.ledvance.com/guarantee

For further products and actual information concerning LED lamps see

- ▶ www.ledvance.com/ledlamps

DISCLAIMER

Subject to change without notice. Errors and omission excepted. Always make sure to use the most recent release.