SMD RTC Crystal Oscillators 7.0 x 5.0 x 1.3 mm 7WZ Series

Features


- · Meet 32.768 kHz RTC clock signal for tight tolerance requirement.
- · Easy to use SMD seam sealed ceramic package.
- · 4 pads design to achieve good soldering contact on PCB.
- · Use AT crystal as the resonator for good temperature performance.
- · Tri-State function available for power saving.
- · RoHS Compliant / Pb Free.

Electrical Specifications



Item / Type	7WZ
Norminal Frequency	32.768 kHz
Oscillation Mode	AT Fundamental
Output Type	CMOS
Output Load	15 pF, or specify
Supply Voltage	1.8 V , 2.5 V , 2.8 V , 3.3V
Frequency Stability	± 25 ppm , ± 50 ppm
Operating Temperature Range	-10 ~ + 70 °C , - 40 ~ + 85 °C
Storage Temperature Range	- 55 ~ + 125 ℃
Voltage Vol (Max.) / Voh (Min.)	0.1 VDD / 0.9 VDD
Rise (Tr)/Fall (Tf) Time	250 ns Max.
Current Consumption	3 mA Max.
Symmetry	45 ~ 55 %

Dimensions




Start-up Time Tri-state Voltage Vol (Max.) / Voh (Min.)

Aging (at 25 °C)









PAD FUNCTION:


1: ENABLE CONTROL

10 ms Max.

0.3 VDD / 0.7 VDD

± 5 ppm at first year

- 2: GND
- 3: OUT
- 4: VDD



Units: mm

Remark : Specification subject to change without prior notice. Please confirm with our sales.