



**CT2300: Full offering DMM accessory kit for Electrical or Electronic Applications. Work well with both bench and handheld meters**



Full offering of accessories for Electrical or Electronic Applications. Both large and micro-sized probe bodies, flexible pincer clip for long reach applications, fully insulated alligator clips for over-sized lugs or fine wires, and spade lug or banana plug adapters for fixed terminal connections. All this utility while meeting the latest international safety standards.

- IEC 61010-031 rated accessories
- PVC jacketed lead wire
- Replaceable Tip Probe - 4mm cage spring and 2mm smooth tip
- Cap on 4mm cage spring tip provides CAT III on probe bodies
- Ø 0.7mm SS Spring Tip probe for fine work
- Extra large alligator clips for electrical work

Kit Contains:

- (2) Modular probes, (1) Black (1) Red
- (2) Flex Pincer Clips, (1) Black (1) Red
- (2) Extra-Large Insulated Alligator Clip, (1) Black (1) Red
- (2) 4mm Banana Plug to Banana Jack Adapter, (1) Black (1) Red

(2) Spring Tip Mini-Probe, (1) Black (1) Red  
 (2) 6mm Spade Lug Adapter, (1) Black (1) Red  
 (2) Banana Test Leads, 4mm Sheath Plug to Right-Angle Sheath Plug, PVC Jacket, 100 cm (40"), (1) Black (1) Red

Probe Bodies	1,000 V CAT III w/cap (CAT II w/o), 36 A
Flex Pincers Clips	1,000 V CAT II
ExLg Alligator Clips	1,000 V CAT III / 600 V CAT IV, 36 A
Plug Adapter	33 Vac / 70 Vdc, 10 A
Spring Tip Probe Bodies	600 V CAT II, 1 A
Spade Lug	33 Vac / 70 Vdc, 10 A
Test Leads	1,000 V CAT III / 600 V CAT IV, 20 A
Temperature	-20 °C to +80 °C
RoHS (2011/65/EU)	Compliant