

PRODUCT SPECIFICATION

EN#: 4711552151527

SD-9314 17 in 1 Tool Kit for Apple Products



Safety and environmental protection:

- RoHS & Pb free: RoHS

Handle:

- Material of handle: TPR, Nylon

Bits:

- Torx


| The first type symbol | Head Specifications | 六角對邊尺寸 | Surface Finish | Bit Length (mm) | Material |
|--|---------------------|--------|----------------|-----------------|--|
|  Torx | T4 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |
|  Torx | T5 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |
|  Torx | T6 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |

| | | | | | |
|--|-----|-----|---------------|----|---|
| | | | | | 8660 |
|  Torx | T8 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |
|  Torx | T10 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |
|  Torx | T15 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |
|  Torx | T20 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |



- specification contents

| The first type symbol | Head Specifications | 六角對邊尺寸 | Surface Finish | Bit Length (mm) | Material |
|--|---------------------|--------|----------------|-----------------|---|
|  Phillips | PH000 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |
|  Slotted | SL1.5mm | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |


- content

| The first type symbol | Head Specifications | Hexagonal edge size | Surface Finish | Bit Length (mm) | Material |
|--|---------------------|---------------------|----------------|-----------------|---|
|  5-Lobe star tip | P2 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |

- content

| The first type symbol | Head Specifications | Hexagonal edge size | Surface Finish | Bit Length (mm) | Material |
|---|---------------------|---------------------|----------------|-----------------|---|
|  Hex | H 1.5 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |
|  Hex | H 2.0 | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI 8660 |

- content

| The first type symbol | Head Specifications | Hexagonal edge size | Surface Finish | Bit Length (mm) | Material |
|---|---------------------|---------------------|----------------|-----------------|---|
|  Needle type bits | Needle | 4mm | Sand blasting | 28 | Nickel-chromium-molybdenum alloy steel AISI |

Product Weight (w/o package):

| Weight(g) | Measurement | | |
|-----------|-------------|-------|-------|
| 142.8 | L(mm) | W(mm) | H(mm) |
| | 151 | 103 | 30 |

Individual Packing

- Packing: Color Sleeve Shrink

Master Packing:

| | Pieces | N.W. (Kg) | G.W. (Kg) | Measurement | | | CUFT |
|--------------------|--------|--------------|--------------|-------------|-------|-------|------|
| | | | | L(cm) | W(cm) | H(cm) | |
| Individual Packing | 1 | - | 0.162 | 15.3 | 10.3 | 3 | - |
| Inner Box | 12 | 1.73 | 2.04 | 31 | 16.3 | 13.5 | 0.24 |
| CTN | 72 | 12.5 | 13.5 | 51 | 33 | 29 | 1.72 |