# 3M<sup>™</sup> 4-Wall, Tripolarized Header

.050" × .100" Latch/Ejector, PTH & SMT Straight, PTH Right Angle

810 Series



- Tripolarization to mating socket
- 50 mil × 100 mil halves the connector length
- Latch and eject for rugged high performance applications
- Available for thru hole or surface mount attachment
- High temperature plastic
- Four-wall shroud provides contact protection
- Contacts: 20, 26, 36, 40, 50, 60, 68, 80 and 100
- RoHS\* compliant version available (RB plating suffix)

Date Modified: September 2, 2005

TS-0253-29 Sheet 1 of 7

## **Physical**

#### Insulation

Material: High Temperature Plastic (LCP)

Flammability: UL 94V-0

Color: Black (RoHS compliant) or Natural

Contact

Material: Copper Alloy

**Plating** 

Underplating:  $100 \mu''$  [  $2.54 \mu m$  ] Nickel Wiping Area:  $30 \mu'' [0.76 \mu m]$  Gold

 $300~\mu^{\prime\prime}$  [7.6  $\mu m$  ] Matte Tin (RoHS compliant) or Tin-Lead (see ordering information) Solder Tails:

Terminal Finish Indicator: e3 (ref JESD97)

Marking: 3M Logo, Part Number and Orientation Triangle

### **Electrical**

Current Rating: 0.5 A

Insulation Resistance:  $> 1 \times 10^9 \Omega$  at 500 Vdc Withstanding Voltage: 500 Vrms at Sea Level


## **Environmental**

**Temperature Rating:** -55°C to +105°C

Process Rating: Maximum 260°C (per J-STD-020C)

Moisture Sensitivity Level: 1 (per J-STD-020C)

\* RoHS = Directive 2002/95/EC, Restriction of the Use of Certain Hazardous Substances in Electrical and Electronic Equipment "RoHS compliant" means that the product or part does not contain any of the following substances in excess of the following maximum concentration values in any homogeneous material, unless the substance is in an application that is exempt under RoHS: (a) 0.1% (by weight) for lead, mercury, hexavalent chromium, polybrominated biphenyls or prolybromianted diphenyl ethers; or (b) 0.01% (by weight) for cadmium. Unless otherwise stated by 3M in writing, this information represents 3M's knowledge and belief based upon information provided by third party suppliers to 3M. UL File No.: E68080



800-225-5373

.050" × .100" Latch/Ejector, PTH & SMT Straight, PTH Right Angle

810 Series





Table 3	
Ejector Latches	Dimension E Min
None	.575 [14.61]
Long	1.010 [25.65]
Short	.885 [22.48]

\*Solder Thief Solder Pads required only on Solder side of PC Board.

#### View A




#### Notes:

- 1. Recommended to process PC Boards through the solder bath such that the connector enters end first (two solder tails at a time). This will help prevent solder bridging.
- 2. A Dummy or Solder Thief Solder Pad at the end of each row is recommended on the bottom or solder side of the PC. Board in order to help prevent solder bridging on the end solder tails. The solder thiefs are only required on the end of the rows which leave the solder bath last.


3. In order to facilitate flow soldering. It is recommended that ejector latches be installed after the soldering process.


TS-0253-29 Sheet 3 of 7

Table 1 **Dimensions** Contact Qty C Short Ref C Long Ref D 020 1.060 [26.92] .722 [18.34] 1.671 [42.44] 1.842 [46.77] .860 [21.84] 026 1.210 [30.73] .872 [22.15] 1.817 [46.15] 1.987 [50.47] 1.010 [25.65] 036 1.460 [37.08] 1.122 [28.50] 2.070 [52.58] 2.274 [57.76] 1.260 [32.00] 040 1.560 [39.62] 1.222 [31.04] 2.170 [55.12] 2.365 [60.07] 1.360 [34.54] 050 1.810 [45.97] 1.472 [37.39] 2.421 [61.49] 2.609 [66.27] 1.610 [40.89] 060 2.060 [52.32] 1.722 [43.74] 2.671 [67.84] 2.872 [72.95] 1.860 [47.24] 068 2.260 [57.40] 1.922 [48.82] 2.870 [72.90] 3.083 [78.31] 2.060 [52.32] 2.360 [59.94] 080 2.560 [65.02] 2.222 [56.44] 3.178 [80.72] 3.370 [85.60] 100 3.060 [77.72] 2.722 [69.14] 3.676 [93.37] 3.875 [98.43] 2.860 [72.64] Table 2 "F" Solder Tail Length ± .010 PCB Thickness .310 .062 [15.7] .090 [2.29] [7.87] See Note 1-.094 [2.39] .112 [2.79] Position 2 .125 [3.18] .143 [3.63] extstyle ext100 Ref .015 X .015 [2.54] [0.38]X[0.38] .265 [6.73] .050 Typ [1.27] -140 ± .010 (See Table 2)  $.165 \pm .010$ .440 ± .010 [4.19] [11.18] .828 Ret .620 Ref .405 [15.75] [10.29].015 Notes: [0.38]1. This polarization bump does not exist 2X .092 .015 X .015 on the 20 position header. [2.34][0.38]X[0.38] Optional: Press 2. Recommended to be mated to the Position 1 Orientation Triangle 2X ⊘.116 fit post mount .050" x .100" 82XXX Series Socket. [2.95]alignment feature **Ordering Information Ejector Latch** Header Long 81XXX-6X0X0X-XX 3505-28 (natural) 3505-28B (black) Contact Quantity (See Table 1) Short Plating suffix: blank = tin lead tails 3505-29 (natural) Board Mounting Options: Ejector/Latch System: RB = matte tin tails 1 = None 3505-29B (black) 0 = None(RoHS compliant) 3 = Press fit posts both ends 5 = With Short Ejectors Installed 6 = With Long Ejector latches Installed Contact Tail: (See Table 2) 2 = Solder Tail for .062 [ 1.57 ] PC Board 3 = Solder Tail for .094 [ 2.39 ] PC Board TS-0253-29 4 = Solder Tail for .125 [ .318 ] PC Board Sheet 4 of 7



.050" × .100" Latch/Ejector, PTH & SMT Straight, PTH Right Angle





#### **Important Notice**

All statements, technical information, and recommendations related to 3M's products are based on information believed to be reliable, but the accuracy or completeness is not guaranteed. Before using this product, you must evaluate it and determine if it is suitable for your intended application. You assume all risks and liability associated with such use. Any statements related to the product which are not contained in 3M's current publications, or any contrary statements contained on your purchase order shall have no force or effect unless expressly agreed upon, in writing, by an authorized officer of 3M.

# **3M**

**Electronics** 

6801 River Place Blvd. Austin, TX 78726-9000 800/328-1368 www.3M.com/electronics

#### Warranty; Limited Remedy; Limited Liability.

This product will be free from defects in material and manufacture for a period of 90 days from the time of purchase. 3M MAKES NO OTHER WARRANTIES INCLUDING, BUT NOT LIMITED TO, ANY IMPLIED WARRANTY OF MERCHANTABILITY OR FITNESS FOR A PARTICULAR PURPOSE. If this product is defective within the warranty period stated above, your exclusive remedy shall be, at 3M's option, to replace or repair the 3M product or refund the purchase price of the 3M product. Except where prohibited by law, 3M will not be liable for any indirect, special, incidental or consequential loss or damage arising from this 3M product, regardless of the legal theory asserted.



Minimum 10% Post-Consumer Fiber Printed in USA.

© 3M 2005