

# PRODUCT SPECIFICATION

EN#: 4710810384059

**1PK-SD006**

**6 In 1 Magnetic Quick Change Screwdriver**



## Safety and environmental protection:

- RoHS & Pb free: RoHS

## Handle:

- Material of handle: PP, TPR
- Handle O.D. (mm): 38

## Blade:





- Material of blade: Chrome vanadium steels SAE(AISI) 6150
- Color of blade: Primary colors
- Blade hardening: Quench hardening process
- Hardness of blade (HRC): 50±2
- Shape of blade: Round head
- Magnetic tips: Yes

## Bits:

- 延長桿\_規格內容

鐵桿外徑 D2 (mm)	本體電鍍	全長 L (mm)	材質打印	PK LOGO打印	球型雙用設計	快拆裝置	滾珠裝置	Joints binding mode
10.8	shine-sided	115	Non	Non	Non	Non	Yes	Ball

- specification contents

The first type symbol (a)	Head Specifications	The first type symbol (b)	Head Specifications	Surface Finish	Bit Length (mm)	鐵桿規格 打印	鐵桿材質 打印	Joints binding mode
 Soltted	SL 5mm	 Phillips	PH 1	bright	75	Yes	Non	Ball
 Soltted	SL 6mm	 Phillips	PH 2	bright	75	Yes	Non	Ball

**Product Weight (w/o package):**

Weight(g)	Measurement		
0	L(mm)	W(mm)	H(mm)

**Individual Packing**

- Packing: Blister Card

**Master Packing:**

	Pieces	N.W. (Kg)	G.W. (Kg)	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0.2	0	0	0	-
Inner Box	20	0	0	0	0	0	0
CTN	60	13	14	37.5	27.5	44.5	1.62