


- Wide 2:1 input voltage 30 W DC/DC converter in a 2 × 1 " plastic case
- I/O isolation 5000 VACrms rated for 250 VACrms working voltage
- Certification according to IEC/EN/ES 60601-1 3rd edition for 2×MOPP
- Risk management process according to ISO 14971 including risk management file
- Acceptance criteria for electronic assemblies according to IPC-A-610 Level 3
- Low leakage current < 2.5 μ A
- Extended operating temperature range -40°C to 80°C.
- EMC compliance to IEC 60601-1-2 4th edition and EN55032 class A
- Operating up to 5000m altitude
- 5 year product warranty



The THM-30 series is a range of medical 30 Watt DC/DC converters in 2.0" x 1.0" plastic package and with wide 2:1 input voltage range. They provide a reinforced isolation system for 5000 VACrms isolation and a very low leakage current of less than 2.5 μ A. The units are approved to IEC/EN/ES 60601-1 3rd edition for 2 × MOPP (Means Of Patient Protection) and come along with an ISO 14971 risk management file. Design and production conform to the quality management system ISO 13485. With a high efficiency of up to 90% and highest grade components the converters can reliably operate in an ambient temperature range of -40°C up to +80°C. They constitute a reliable solution not only for medical equipment but also for demanding ranges of application such as transportation, control & measurement or IGBT drivers.

Models				
Order code	Input voltage range	Output voltage	Output current max.	Efficiency typ.
THM 30-1211	9.0 – 18 VDC (12 VDC nominal)	5.0 VDC	6000 mA	88.5 %
THM 30-1212		12 VDC	2500 mA	88.5 %
THM 30-1213		15 VDC	2000 mA	88.5 %
THM 30-1215		24 VDC	1250 mA	89.0 %
THM 30-1221		±5 VDC	±3000 mA	86.0 %
THM 30-1222		±12 VDC	±1250 mA	88.5 %
THM 30-1223		±15 VDC	±1000 mA	88.5 %
THM 30-2411	18 – 36 VDC (48 VDC nominal)	5.0 VDC	6000 mA	88.0 %
THM 30-2412		12 VDC	2500 mA	89.0 %
THM 30-2413		15 VDC	2000 mA	90.0 %
THM 30-2415		24 VDC	1250 mA	88.5 %
THM 30-2421		±5 VDC	±3000 mA	86.0 %
THM 30-2422		±12 VDC	±1250 mA	88.5 %
THM 30-2423		±15 VDC	±1000 mA	89.5 %
THM 30-4811	36 – 75 VDC (48 VDC nominal)	5.0 VDC	6000 mA	89.0 %
THM 30-4812		12 VDC	2500 mA	89.0 %
THM 30-4813		15 VDC	2000 mA	89.0 %
THM 30-4815		24 VDC	1250 mA	89.0 %
THM 30-4821		±5 VDC	±3000 mA	86.5 %
THM 30-4822		±12 VDC	±1250 mA	90.0 %
THM 30-4823		±15 VDC	±1000 mA	89.0 %

Input Specifications

Input current no load	12 Vin models: 18 mA typ. 24 Vin models: 13 mA typ. 48 Vin models: 10 mA typ.	
Surge voltage (3 sec. max.)	12 Vin models: 25 V max. 24 Vin models: 50 V max. 48 Vin models: 100 V max.	
Start-up voltage	12 Vin models: 9 VDC (or lower) 24 Vin models: 18 VDC (or lower) 48 Vin models: 36 VDC (or lower)	
Startup time	60 ms max. (30 ms typ.)	
Under voltage shut down (lock-out circuit)	12 Vin models: 7.8 - 8.6 VDC 24 Vin models: 15.8 - 17.4 VDC 48 Vin models: 32 - 34 VDC	
Input filter	Pi-type	
Conducted noise	– Conducted & Radiated input surpression – Filter proposal	EN 55011 limits to IEC 60601-1-2 4th edition EN55032 class A (internal filter) EN55032 class B with external components tba
EMC immunity	– Generic for Medical equipment – ESD (electrostatic discharge) – Radiated immunity – Fast transient / surge (with external input capacitor / diode) – Conducted immunity – Magnetic field immunity	IEC/EN 60601-1-2 4th edition EN 61000-4-2, air ± 15 kV, contact ± 8 kV, perf. criteria A EN 61000-4-3, 10 V/m, perf. criteria A EN 61000-4-4, ± 2 kV, perf. criteria A EN 61000-4-5, ± 2 kV perf. criteria A 12 Vin models: Nippon chemi-con KY 220 μ F/ 100 V TVS - SMDJ36A, 36V, 3000 W) 24 Vin models: Nippon chemi-con KY 220 μ F/ 100 V TVS - SMDJ58A, 58V, 3000 W) 48 Vin models: Nippon chemi-con KY 220 μ F/ 100 V TVS - SMDJ120A, 120V, 3000 W) EN 61000-4-6, 10 Vrms, perf. criteria A EN 61000-4-8 100 A/m, continuous, perf. criteria A 1000 A/m, 1 sec., perf. criteria A
External input fuse required (recommended values, slow blow type)	12 Vin models: 6.3 A 24 Vin models: 3.15 A 48 Vin models: 1.6 A	

Output Specifications

Voltage set accuracy	$\pm 1\%$ max.	
Output voltage adjustment range (single output models only)	5 & 12 VDC models: $\pm 10\%$ 15 & 24 VDC models: $-10 / +20\%$	
Regulation	– Input variation – Load variation 0 – 100 % – Cross regulation	single output: 0.2 % max. dual output: 0.5 % max. single output: 0.2 % max. dual output: 1.0 % max. dual output: 5.0 % max. (asymmetrical load 25/100%)
Temperature coefficient	$\pm 0.02\%$ /K typ.	
Minimum load	not required	
Ripple and noise (20 MHz Bandwidth)	(\pm)5.0 VDC models: 50 mVp-p typ. with cap. 10 μ F/25V X7R MLCC (\pm)12 VDC models: 75 mVp-p typ. with cap. 10 μ F/25V X7R MLCC ± 15 VDC models: 75 mVp-p typ. with cap. 10 μ F/25V X7R MLCC 15 VDC models: 100 mVp-p typ. with cap. 10 μ F/25V X7R MLCC 24 VDC models: 100 mVp-p typ. with cap. 4.7 μ F/50V X7R MLCC	
Transient response	– Recovery time (25% load step change)	250 μ s typ.

General Specifications


Overload protection		at 150 % typ. of I _{out} rated (hiccup mode)
Short-circuit protection		Continuous, automatic recovery
Overvoltage protection	(±)5.0 VDC models: (±)12 VDC models: (±)15 VDC models: 24 VDC models:	6.2 VDC typ. 15 VDC typ. 20 VDC typ. 30 VDC typ.
Capacitive load	– Single output	5.0 VDC models: 7'200 µF max. 12 VDC models: 1'200 µF max. 15 VDC models: 1'000 µF max. 24 VDC models: 375 µF max.
	– Dual output	±5 VDC models: 3'600 µF max. (each output) ±12 VDC models: 750 µF max. (each output) ±15 VDC models: 500 µF max. (each output)
Temperature ranges	– Operating	–40°C to +80°C
	– Case temperature	+105°C max.
	– Storage temperature	–55°C to +125°C
Derating	(±)5 VDC models: other models:	1.67%/K above 55°C 2%/K above 45°C
Overtemperature protection		at 115°C typ.
Thermal impedance		12.85 °C/W
Humidity (non condensing)		5 % to 95 % rel H max.
Isolation voltage (50Hz, 60s)		5000 VACrms reinforced
Clearance/creepage		8 mm min.
Leakage current (at 240VAC, 60Hz)		2.5 µA max.
Isolation capacitance (input/output)		20 pF typ.
Altitude during operation		5000 m
Temperature coefficient		±0.02 %/K typ.
Reliability, calculated MTBF (MIL-HDBK-217F at +25°C, ground benign)		tbd
Switching frequency		250 kHz typ. (pulse width modulation)
Vibration and thermal shock resistance		according to MIL-STD-810F
Safety standards/approvals – Medical equipment		ANSI/AAMI ES 60601-1:2005/(R)2012, IEC/EN 60601-1 3rd edition
	– Certification documents	tba
Environmental compliance	– Reach	www.tracopower.com/products/reach-declaration.pdf
	– RoHS	RoHS directive 2011/65/EU

Physical Specifications

Casing material	non-conductive plastic
Base material	non-conductive plastic
Potting material	silicone (UL94 V-0 rated)
Package weight	32 g (1.13oz)
Soldering temperature	max. 265°C / 10 s

All specifications valid at nominal input voltage, full load and +25°C after warm-up time unless otherwise stated.

Outline Dimensions



Pinout		
Pin	Single	Dual
1	+Vin (Vcc)	+Vin (Vcc)
2	-Vin (GND)	-Vin (GND)
3	+Vout	+Vout
4	-Vout	Common
5	Trim	-Vout

Dimensions in [mm], () = Inch
 Tolerances ± 0.5 (± 0.02)
 ± 0.25 (± 0.01)
 Pin pitch tolerances ± 0.25 (± 0.01)
 Pin \varnothing 1.0 ± 0.1 (0.04 ± 0.004)