

# PRODUCT SPECIFICATION

EN#: 4710810409851

## SD-9810A 10 in 1 Auto Loading Ratchet Screwdriver Set (Unit:25Pcs/Set)



### Safety and environmental protection:

- RoHS & Pb free: RoHS

### Handle:

- Material of handle: PC, PVC
- Handle O.D. (mm): 30.3

### Blade:

- Material of blade: Chrome molybdenum alloy steel AISI 8660
- Color of blade: Primary colors
- Blade hardening: Quench hardening process
- Hardness of blade (HRC): 55±3
- Shape of blade: Round head
- Magnetic tips: Non

### Bits:

- Torx

The first type symbol	Head Specifications	六角對邊尺寸	Surface Finish	Bit Length (mm)	Color	規格打印	材質打印
 Torx	T5	4mm	bright	28	Non	Yes	Non
 Torx	T6	4mm	bright	28	Non	Yes	Non
 Torx	T8	4mm	bright	28	Non	Yes	Non
 Torx	T10	4mm	bright	28	Yes	Non	

- specification contents

The first type symbol	Head Specifications	六角對邊尺寸	Surface Finish	Bit Length (mm)	本體色環	規格打印	材質打印
 Phillips	PH00	4mm	bright	28	Non	Yes	Non
 Phillips	PH0	4mm	bright	28	Non	Yes	Non
 Phillips	PH1	4mm	bright	28	Non	Yes	Non
 Slotted	SL1.5mm	4mm	bright	28	Non	Yes	Non
 Slotted	SL2.0mm	4mm	bright	28	Non	Yes	Non
 Slotted	SL3.0mm	4mm	bright	28	Non	Yes	Non

**Product Weight (w/o package):**

Weight(g)	Measurement		
0	L(mm)	W(mm)	H(mm)

**Individual Packing**

- Packing:

**Master Packing:**

	Pieces	N.W. (Kg)	G.W. (Kg)	Measurement			CUFT
				L(cm)	W(cm)	H(cm)	
Individual Packing	1	-	0	0	0	0	-
Inner Box	1	0	0	0	0	0	0
CTN	4	10	11.5	45	45	19	1.36