

EPIC® MH Bus PIN 1x(4) contact holder

High flexibility by the use of any combination of inserts in one connector

Info

Stamped gold plated contacts with 0.8mm diameter for D-Sub inserts Shielded modul for data and signal transmission







Wind Energy



Rail



Mechanical and plant engineering



Automation & amp; fältinstallation

Benefits

Shielded modul for data and signal transmission EPIC® MH system is mateable with the market standard Crimp connection for permanent vibration proof contact The mix of different functions in one plug guarantees high flexibility Railway applications

- Fire protection on railway vehicles: Test according EN 45545-2. Requirement sets R22 and R23. Hazard level HL1, HL2 and HI 4



EPIC® MH Bus PIN 1x(4) contact holder

Application range

Mechanical engineering
Robotics industry
Plant engineering
Renewable energy
Railway applications / vehicle construction

Technical Data

Classification: ETIM 5.0 Class-ID: EC002641

ETIM 5.0 Class-Description: Modular connector (industrial

connector)

Rated voltage (V): 50
Rated impulse voltage: 0,8 kV
Rated current (A): 10
Pollution degree: 3

Flammability: UL94 V-0

Number of contacts: 4

Termination methods: Crimp termination: 0.14 - 2.5 mm²

Material: PA
Cycle of mechanical operation: 500

Certifications: UL-tested:

UL File Number: E75770

Temperature range: -40°C

+125°C

Note

Photographs are not to scale and do not represent detailed images of the respective products. Prices are net prices without VAT and surcharges. Sale to business customers only.



EPIC® MH Bus PIN 1x(4) contact holder

Article number	Article description	Contact type	Number of operating contacts
EPIC® MH BUS PIN 1x(4) contact holder			
44423229	EPIC® MHS Bus PIN 1x(4) CM	male	4 + shield
44423231	EPIC® MHB Bus PIN 1x(4) CM	female	4 + shield