

# MRJR Rugged RJ45 Connector

Product Specification S6055C Rev 1.5


Amphenol

*Now you're connected!*


## About Amphenol Commercial Products

Amphenol's commercial connector products are used in a variety of end user applications including networking, telecom, server & computer, storage & HDD, consumer electronics and entertainment, professional audio & Industrial & Military/Aerospace.


## MRJ/MRJR PCB Options




**MRJR-8780-01**  
CAT5e RJ45 on PCB  
with Matching RJ45




**MRJR-5580-01**  
Standard RJ45 on PCB  
with Matching Cable Header




**MRJR-5980-01**  
Standard RJ45 on PCB with  
Matching Terminal Block




**MRJR-5C80-01**  
Standard RJ45 on PCB  
For Discrete Wiring




**MRJR-3461-0F Shown**  
6 Position RJ11,  
Vertical PCB Tail



**MRJR-5381-01 Shown**  
8 Position RJ45,  
Right Angle PCB Tail



**MRJR-5481-0C Shown**  
8 Position RJ45, Vertical PCB  
Tail, Extra Shell Clearance



**MRJR-5381-04 Shown**  
4 Port, 8 Position RJ45,  
Right Angle PCB Tail



## Overview

This product specification defines the general use and performance parameters for Amphenol's MRJR series of connectors.

### Availability:

- Right angle and vertical PCB tail termination with 4, 6, 8, or 10 positions
- Various LED, tail length, & thread options
- Various PCB options including matching RJ connector, cable header, terminal block, or without matching connector for hand wiring (short and long PCB's available)
- EMI ferrite filtering
- Shells with extra clearance about mounting holes for reduced port-to-port spacing
- Single or four port configurations
- Dust covers & IP67 sealing boots for enhanced mating area protection

## Usage

The connector system is designed to provide a standard RJ45 interface, ideal for harsh environments where Ethernet/IP protocol is used. Protection is provided for IP68 applications per IEC 60529 specification. Epoxy free design protects from leakage under extreme temperature changes. Product options compatible with 10BaseT, 100BaseT, and 1000BaseT Ethernet.

## Applications

Intended for use in applications such as:

- Medical equipment
- ATM machines
- Lottery terminals & slot machines
- GPS positioning equipment
- Military vehicles, radios, computers
- Test equipment
- Mobile communication systems
- Traffic control & monitoring systems

*Now you're connected!*

#### About Amphenol Commercial Products

Amphenol's commercial connector products are used in a variety of end user applications including networking, telecom, server & computer, storage & HDD, consumer electronics and entertainment, professional audio & Industrial & Military/Aerospace.

#### Related Products

##### MUSBR-XHD Series




**MUSBR-AHD2-821XX**  
Thumb Screw, Translucent Colour




**MUSBR-AHD2-221XX**  
Cap Screw, Black Colour

##### MUSB Series



**MUSB-B151-34**  
Mini-B USB,  
Right Angle PCB Tail



**MUSB-C111-30**  
Stacked Type-A USB,  
Right Angle PCB Tail

#### Connector Electrical Characteristics

Current Rating:	1.5A per contact
Contact Resistance:	30 mΩ max
Insulation Resistance:	500 MΩ min
Dielectric Withstanding Voltage:	1000/1500 VAC @ sea level
LED Forward DC Current:	25mA max
LED Forward Voltage:	2.5V max @ 20mA
Minimum Impedance (Ferrite):	38Ω @ 25 MHz

#### Connector Mechanical Characteristics

Thermal Shock:	25 cycles @ -40° to +70° C
Physical Shock:	Per EIA364-27, Condition H (11ms 30G)
Humidity:	Per EIC512-6 / EIA364-11A
Vibration:	Per EIA364-28, Condition 5A
Salt Spray:	Per EIA364-26, 250 Hrs
Mating Cycles:	2500
Operating Temperature:	-40°C to +105°C
Temperature Rise:	Meets the requirement of 30°C ΔT

#### Assembly Process Characteristics

Recommended Torque for Panel Mount Screws: 0.45 to 0.65 Nm (4.00 to 5.75 in-lbs).  
Hand or Wave Solder: 150°C for 180 seconds (pre-heat) and 265°C for 8 seconds max (solder tails).  
Solder tails suitable for PCB thickness of 1.57 to 3.18 mm (.062 to 0.125")

#### Material Characteristics

MRJR connectors are RoHS compliant per EU directive 2011/65/EU and amendments. Unless otherwise specified, the materials for each component shall be:

- Contacts: Phosphor Bronze with 1.27μm (50μ") min Gold over 1.27μm (50μ") min Nickel
- Housing: High temperature thermoplastic, UL94V-0 rated, black
- Front Housing: Clear Polycarbonate (customer process cleaners must be compatible)
- Shell: Die-cast Zinc alloy, Nickel plating
- Gasket: Silicone rubber
- LED: Epoxy lens, Tin plating on steel tail

# Now you're connected!

## About Amphenol Commercial Products


Amphenol's commercial connector products are used in a variety of end user applications including networking, telecom, server & computer, storage & HDD, consumer electronics and entertainment, professional audio & Industrial & Military/Aerospace.

## Related Products

### MHDR Series



**MHDR-A511-30**  
Type-A HDMI,  
Vertical PCB Tail



**MHDR-A111-30**  
Type-A HDMI,  
Right Angle PCB Tail

### MUSBR Series



**MUSBR-A511-40**  
Type-A USB, Vertical  
PCB Tail, Low-Profile

### MDBR Series



**MDBR-E09SM-AN0**  
9-Size Socket D-Sub,  
Solder Cup

## Available Documents

### Drawing Numbers:

P-MRJR-33XX-X1	MRJR Receptacle, Right Angle, 4 or 6 position, LED, Tail Length, & Thread Options
P-MRJR-34XX-XF	MRJR Receptacle, Vertical, 4 or 6 position, LED, Tail Length, & Thread Options
P-MRJR-37XX-X1	MRJR Receptacle, Right Angle on PCB with RJ45 Adapter, 4 or 6 position, LED & Thread Options
P-MRJR-53XX-X1	MRJR Receptacle, Right Angle, 8 or 10 position, LED, Tail Length, & Thread Options
P-MRJR-53XX-X4	MRJR Receptacle, Right Angle, 8 or 10 position, LED, Tail Length, & Thread Options, 4-Port
P-MRJR-53XX-XC	MRJR Receptacle, Right Angle, 8 or 10 position, LED, Tail Length, & Thread Options, Extra Shell Clearance
P-MRJR-54XX-XC	MRJR Receptacle, Vertical, 8 or 10 position, LED, Tail Length, & Thread Options, Extra Shell Clearance
P-MRJR-54XX-XF	MRJR Receptacle, Vertical, 8 or 10 position, LED, Tail Length, and Thread Options
P-MRJR-578X-X1	MRJR Receptacle, Right Angle on PCB with RJ45 Adapter, 8 Position, LED & Thread Options
P-MRJR-578X-XC	MRJR Receptacle, Right Angle on PCB with RJ45 Adapter, 8 Position, LED & Thread Options, Extra Shell Clearance
P-MRJR-588X-X1	MRJR Receptacle, Right Angle on PCB with Vertical RJ45 Adapter, 8 Position, LED & Thread Options
P-MRJR-59XX-X1	MRJR Receptacle, Right Angle on PCB with Terminal Blocks, 8 or 10 Position, LED & Thread Options
P-MRJR-5AXX-X1	MRJR Receptacle, Right Angle on Short PCB for Wiring, 8 or 10 Position, LED & Thread Options
P-MRJR-5CXX-X1	MRJR Receptacle, Right Angle on PCB for Wiring, 8 or 10 Position, LED & Thread Options
P-MRJR-5D80-X1	MRJR Receptacle, Right Angle on PCB with 2 x 5 Vertical Header, 8 Position, Thread Options
P-MRJR-63XX-X1	MRJR Receptacle, Right Angle, EMI Filtered, 8 or 10 position, LED, Tail Length, & Thread Options
P-MRJR-878X-X1	MRJR Receptacle, Cat5e, Right Angle on PCB with RJ45 Adapter, 8 Position, LED & Thread Options

### Report Numbers:

QTR9300463	Qualification Test Report for MRJR-5380-011
QTR9300519	Qualification Test Report for MRJR-3463-MF

Contact Factory, authorized Amphenol representative or website [www.amphenolcanada.com](http://www.amphenolcanada.com) for additional configurations.

# Now you're connected!

## Product Numbering System

Series	MRJR	-	X	X	X	X	-	X	X	X
<b>Series</b>	MRJR									
	Rugged RJ Series, Generation 2									
<b>Modular Jack Type</b>										
3	RJ11, 6 Position <sup>1</sup>									
4	RJ11, 6 Position with EMI Ferrite Filtering <sup>2</sup>									
5	RJ45, 8 or 10 Position <sup>3</sup>									
6	RJ45, 8 or 10 Position with EMI Ferrite Filtering <sup>2</sup>									
7	RJ45, 8 or 10 Position with Transient Voltage Suppression <sup>4</sup>									
8	RJ45, 8 Position with Cat5e Performance Level <sup>4</sup>									
<b>Termination Style</b>										
3	Right Angle									
4	Vertical									
5	Right Angle on PCB with Right Angle Cable Header <sup>5</sup>									
7	Right Angle on PCB with Right Angle RJ45 Modular Jack <sup>6</sup>									
8	Right Angle on PCB with Vertical RJ45 Modular Jack <sup>7</sup>									
9	Right Angle on PCB with Terminal Blocks									
A	Right Angle on PCB with Holes with Wiring (Style 5 PCB) <sup>8</sup>									
B	Right Angle on PCB with Vertical Cable Header <sup>9</sup>									
C	Right Angle on PCB with Holes for Wiring (Style 7 PCB) <sup>8</sup>									
D	Right Angle on PCB with Vertical Cable Header <sup>9</sup>									
<b>Number of Contacts</b>										
4	4 Contacts		8	8 Contacts						
6	6 Contacts		A	10 Contacts						
<b>LED Options</b>										
0	No LED's		6	Yellow Left, Yellow Right						
1	Green Left, Yellow Right		A	Bi-colour Green/Yellow Left & Right						
4	Yellow Left, Green Right		D	Green Left, Bi-colour Green/Yellow Right						
5	Green Left, Green Right		E	Yellow Left, Bi-colour Green/Yellow Right						
<b>Tail Length &amp; Thread Options</b>										
0	2.54mm (.100") Tail Length, #4-40 UNC Thread									
B	3.81mm (.150") Tail Length, #4-40 UNC Thread									
M	2.54mm (.100") Tail Length, M3 x 0.5 Thread									
P	3.81mm (.150") Tail Length, M3 x 0.5 Thread									
<b>Other Options<sup>10</sup></b>										
1	1 port (vertical has through hole mounting, right angle has threaded lug)									
4	4 port (right angle connector, threaded lug mounting)									
C	1 port, extra clearance near shell mounting holes									
F	1 port (vertical connector, threaded lug mounting)									
<b>Unique Special Code</b>										
No Digit	No Digit - Part defined by previous 10 digits									
1 to 9	1 to 9 - Unique special feature									

### Notes

- Term RJ11 refers to jack for 6P2C, 6P4C or 6P6C (RJ11, RJ12, RJ13, RJ14, RJ18 or RJ25).
- Ferrite option currently available for right angle connectors only.
- Term RJ45 refers to non-keyed jack for 8P8C or 10P10C (RJ31, RJ38, RJ48C, RJ49, RJ50, RJ61).
- Transient voltage suppression and Cat5e performance level for connectors on a PCB only. Consult with Amphenol for availability.

- Termination style 5 suitable for both RJ11 and RJ45 jacks. Consult with Amphenol regarding applications where a smaller 14 pin cable header would be preferred.
- Termination style 7 currently available for RJ11 (6P4C & 6P6C) and RJ45 (8P8C) only.
- Termination style 8 currently available for RJ45 (8P8C) only.
- Termination style A uses the PCB from termination style 5. Termination style C uses the PCB from termination style 7.
- Termination styles B & D currently available for RJ11 (6P4C & 6P6C) without LED's and RJ45 (8P8C) without LED's only.
- Consult with Amphenol for additional termination styles, solder cup contacts, LED colours, contact tail lengths, mounting styles, non-conductive gaskets or other requirements of interest. See catalogue Accessories pages for dust cover and plug boot options.

Amphenol Canada Corp.

Page 4 of 4

605 Milner Avenue  
Toronto, Ontario, Canada, M1B 5X6  
+1 416 291 4401

Copyright © Amphenol Corporation 2017 • All rights reserved

www.amphenolcanada.com