

## 73412W Multi-Conductor - 600V Unshielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles



For more Information  
please call

1-800-Belden1

### General Description:

14 AWG stranded (41x30) bare copper conductors, PVC insulation, oil-resistant PVC jacket.

### Physical Characteristics (Overall)

#### Conductor

AWG:

# Conductors	AWG	Stranding	Conductor Material
11	14	41x30	BC - Bare Copper

Total Number of Conductors: 12

#### Ground Wire

Ground Wire (Y/N): Y

Ground Wire AWG: 14

Ground Wire Stranding: 41x30

Ground Wire Conductor Material: BC - Bare Copper

Ground Wire Insulation Material: PVC - Polyvinyl Chloride

#### Insulation

Insulation Material:

Insulation Material	Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.022

Insulation Color Code Chart:

Color	Description
Black	Individually Numbered

#### Outer Shield

Outer Shield Material:

Outer Shield Material
Unshielded

#### Outer Jacket

Outer Jacket Material:

Outer Jacket Material	Nom. Wall Thickness (in.)
PVC - Polyvinyl Chloride	0.085

#### Overall Cable

Overall Nominal Diameter: 0.667 in.

### Mechanical Characteristics (Overall)

Storage Temperature Range: -40°C To +90°C

Installation Temperature Range: Flexing: -5°C To +90°C

Bulk Cable Weight: 590 lbs/1000 ft.

Max. Recommended Pulling Tension: 386 lbs.

Min. Bend Radius/Minor Axis: 3.300 in.

Min. Bend/Installation: 3.300 in.

Min. Bend Radius (Continuous Flexing): 3.300 in.

Flex Cycle Rating: 1 Million Flexes

### Applicable Specifications and Agency Compliance (Overall)

#### Applicable Standards & Environmental Programs

AWM Specification: UL Style 2587 (600 V 90°C)

CSA Specification: 600 V AWM I/II A/B

EU Directive 2011/65/EU (ROHS II): Yes

MIL Order #39 (China RoHS): Yes

Other Specification: VDE 0472, Section 803 Oil Test, EU Low Voltage Directive 2014/35/EC, EU Directive 2011/65/EU(RoHS2), REACH Regulation (EC 1907/2006), California Proposition 65

#### Flame Test

## ENGLISH MEASUREMENT VERSION

### 73412W Multi-Conductor - 600V Unshielded, Light to Moderate Flexing Applications Up to 1 Million Flex Life Cycles

CSA Flame Test: F11

#### Suitability

Suitability - Burial: Yes

#### Electrical Characteristics (Overall)

##### Nom. Inductance:

Inductance (µH/ft)

0.170

##### Max. Capacitance Conductor to Conductor:

Freq. (MHz) Capacitance (pF/ft)

0.001 36.000

##### Nom. Conductor DC Resistance:

DCR @ 20°C (Ohm/1000 ft)

2.600

##### Max. Operating Voltage - UL:

Voltage

600V

#### Put Ups and Colors:

Item #	Putup	Ship Weight	Color	Notes	Item Desc
73412W 008100	100 FT	67.100 LB	GRAY		14AWG 41/30 12C UNSHIELDED
73412W 0081000	1,000 FT	647.000 LB	GRAY		14AWG 41/30 12C UNSHIELDED
73412W 008500	500 FT	336.000 LB	GRAY		14AWG 41/30 12C UNSHIELDED

Revision Number: 0 Revision Date: 09-27-2017

© 2017 Belden, Inc.  
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described herein are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability. Belden provides the information and specifications herein on an "AS IS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein. All sales of Belden products are subject to Belden's standard terms and conditions of sale.