


SAFETY DATA SHEET
Electrolube IPA Cleaning Wipes x100

According to Appendix D, OSHA Hazard Communication Standard 29 CFR §1910.1200

1. Identification**Product identifier****Product name** Electrolube IPA Cleaning Wipes x100**Product number** EIPA100, ZE**Recommended use of the chemical and restrictions on use****Application** Cleaning agent.**Uses advised against** No specific uses advised against are identified.**Details of the supplier of the safety data sheet****Supplier**ELECTROLUBE. A division of HK WENTWORTH LTD
HK WENTWORTH-AMERICA
PO Box 126257
Benbrook, Texas 76126
USA
info@hkw.us.com
+1 888-501-9203**Emergency telephone number****Emergency telephone** +1 202 464 2554 (USA only)
+44 1235 239670**2. Hazard(s) identification****Classification of the substance or mixture****Physical hazards** Flam. Liq. 2 - H225**Health hazards** Eye Irrit. 2A - H319 STOT SE 3 - H336**Environmental hazards** Not Classified**Label elements****Pictogram****Signal word** Danger**Hazard statements** H225 Highly flammable liquid and vapor.
H319 Causes serious eye irritation.
H336 May cause drowsiness or dizziness.

Electrolube IPA Cleaning Wipes x100

Precautionary statements	<p>P210 Keep away from heat, sparks, open flames and hot surfaces. No smoking.</p> <p>P240 Ground/ bond container and receiving equipment.</p> <p>P241 Use explosion-proof electrical equipment.</p> <p>P242 Use only non-sparking tools.</p> <p>P243 Take precautionary measures against static discharge.</p> <p>P261 Avoid breathing vapor/ spray.</p> <p>P264 Wash contaminated skin thoroughly after handling.</p> <p>P271 Use only outdoors or in a well-ventilated area.</p> <p>P280 Wear protective gloves/ protective clothing/ eye protection/ face protection.</p> <p>P303+P361+P353 If on skin (or hair): Take off immediately all contaminated clothing. Rinse skin with water/ shower.</p> <p>P304+P340 If inhaled: Remove person to fresh air and keep comfortable for breathing.</p> <p>P305+P351+P338 If in eyes: Rinse cautiously with water for several minutes. Remove contact lenses, if present and easy to do. Continue rinsing.</p> <p>P312 Call a poison center/ doctor if you feel unwell.</p> <p>P337+P313 If eye irritation persists: Get medical advice/ attention.</p> <p>P370+P378 In case of fire: Use foam, carbon dioxide, dry powder or water fog to extinguish.</p> <p>P403+P233 Store in a well-ventilated place. Keep container tightly closed.</p> <p>P403+P235 Store in a well-ventilated place. Keep cool.</p> <p>P405 Store locked up.</p> <p>P501 Dispose of contents/ container in accordance with national regulations.</p> <p>P102 Keep out of reach of children.</p>
---------------------------------	---

Contains Propan-2-ol

Other hazards

This product does not contain any substances classified as PBT or vPvB.

3. Composition/information on ingredients

Mixtures

<p>Propan-2-ol</p> <p>CAS number: 67-63-0</p>	30-60%
<p>Classification</p> <p>Flam. Liq. 2 - H225</p> <p>Eye Irrit. 2A - H319</p> <p>STOT SE 3 - H336</p>	

The full text for all hazard statements is displayed in Section 16.

4. First-aid measures

Description of first aid measures

General information	Get medical attention if any discomfort continues. Show this Safety Data Sheet to the medical personnel.
Inhalation	Move affected person to fresh air and keep warm and at rest in a position comfortable for breathing. Maintain an open airway. Loosen tight clothing such as collar, tie or belt. When breathing is difficult, properly trained personnel may assist affected person by administering oxygen. Get medical attention. Place unconscious person on their side in the recovery position and ensure breathing can take place.

Electrolube IPA Cleaning Wipes x100

Ingestion	Rinse mouth thoroughly with water. Give a few small glasses of water or milk to drink. Stop if the affected person feels sick as vomiting may be dangerous. Never give anything by mouth to an unconscious person. Place unconscious person on their side in the recovery position and ensure breathing can take place. Keep affected person under observation. Get medical attention.
Skin Contact	Rinse with water.
Eye contact	Rinse with water. Do not rub eye. Remove any contact lenses and open eyelids wide apart. Get medical attention if any discomfort continues.
Protection of first aiders	First aid personnel should wear appropriate protective equipment during any rescue.

Most important symptoms and effects, both acute and delayed

General information	The severity of the symptoms described will vary dependent on the concentration and the length of exposure.
Inhalation	A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.
Ingestion	No specific symptoms known.
Skin contact	No specific symptoms known.
Eye contact	Irritating to eyes.

Indication of immediate medical attention and special treatment needed

Notes for the doctor	Treat symptomatically.
-----------------------------	------------------------

5. Fire-fighting measures

Extinguishing media

Suitable extinguishing media	The product is flammable. Extinguish with alcohol-resistant foam, carbon dioxide, dry powder or water fog. Use fire-extinguishing media suitable for the surrounding fire.
Unsuitable extinguishing media	Do not use water jet as an extinguisher, as this will spread the fire.

Special hazards arising from the substance or mixture

Specific hazards	Containers can burst violently or explode when heated, due to excessive pressure build-up. Flammable liquid and vapour. Vapors may be ignited by a spark, a hot surface or an ember. Vapors may form explosive mixtures with air. Fire-water run-off in sewers may create fire or explosion hazard.
Hazardous combustion products	Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

Advice for firefighters

Protective actions during firefighting	Avoid breathing fire gases or vapors. Evacuate area. Keep upwind to avoid inhalation of gases, vapors, fumes and smoke. Ventilate closed spaces before entering them. Cool containers exposed to heat with water spray and remove them from the fire area if it can be done without risk. Cool containers exposed to flames with water until well after the fire is out. If a leak or spill has not ignited, use water spray to disperse vapors and protect men stopping the leak. Control run-off water by containing and keeping it out of sewers and watercourses. If risk of water pollution occurs, notify appropriate authorities.
---	--

Electrolube IPA Cleaning Wipes x100

Special protective equipment for firefighters Wear positive-pressure self-contained breathing apparatus (SCBA) and appropriate protective clothing. Standard Firefighter's clothing including helmets, protective boots and gloves will provide a basic level of protection for chemical incidents.

6. Accidental release measures

Personal precautions, protective equipment and emergency procedures

Personal precautions Wear protective clothing as described in Section 8 of this safety data sheet. No action shall be taken without appropriate training or involving any personal risk. Evacuate area. Provide adequate ventilation. No smoking, sparks, flames or other sources of ignition near spillage. Promptly remove any clothing that becomes contaminated. Avoid inhalation of dust and vapors. Use suitable respiratory protection if ventilation is inadequate.

Environmental precautions

Environmental precautions Avoid discharge into drains or watercourses or onto the ground.

Methods and material for containment and cleaning up

Methods for cleaning up Wear protective clothing as described in Section 8 of this safety data sheet. Clear up spills immediately and dispose of waste safely. Eliminate all ignition sources if safe to do so. No smoking, sparks, flames or other sources of ignition near spillage. Do not allow material to enter confined spaces, due to the risk of explosion. Absorb small quantities with paper towels and evaporate in a safe place. Once evaporation is complete, place paper in a suitable waste disposal container and seal securely. Flush contaminated area with plenty of water. Wash thoroughly after dealing with a spillage. For waste disposal, see Section 13.

Reference to other sections For personal protection, see Section 8. See Section 11 for additional information on health hazards. See Section 12 for additional information on ecological hazards. For waste disposal, see Section 13.

7. Handling and storage

Precautions for safe handling

Usage precautions Keep out of the reach of children. Read and follow manufacturer's recommendations. Wear protective clothing as described in Section 8 of this safety data sheet. Keep away from food, drink and animal feeding stuffs. Handle all packages and containers carefully to minimize spills. Keep container tightly sealed when not in use. Avoid the formation of mists. The product is flammable. Keep away from heat, hot surfaces, sparks, open flames and other ignition sources. No smoking. Do not handle until all safety precautions have been read and understood. Do not handle broken packages without protective equipment. Do not reuse empty containers.

Advice on general occupational hygiene Wash promptly if skin becomes contaminated. Take off contaminated clothing and wash before reuse. Wash contaminated clothing before reuse.

Conditions for safe storage, including any incompatibilities

Storage precautions Store locked up. Keep away from oxidizing materials, heat and flames. Keep only in the original container. Keep container tightly closed, in a cool, well ventilated place. Keep containers upright. Protect containers from damage.

Storage class Flammable liquid storage.

Specific end uses(s)

Specific end use(s) The identified uses for this product are detailed in Section 1.

8. Exposure Controls/personal protection

Control parameters

Electrolube IPA Cleaning Wipes x100

Occupational exposure limits

Propan-2-ol

Long-term exposure limit (8-hour TWA): OSHA 400 ppm 980 mg/m³
 Long-term exposure limit (8-hour TWA): ACGIH 200 ppm 492 mg/m³
 Short-term exposure limit (15-minute): ACGIH 400 ppm 984 mg/m³
 A4

OSHA = Occupational Safety and Health Administration.
 ACGIH = American Conference of Governmental Industrial Hygienists.
 A4 = Not Classifiable as a Human Carcinogen.

Propan-2-ol (CAS: 67-63-0)

Immediate danger to life and health 2000 ppm

Exposure controls

Protective equipment



Appropriate engineering controls

Provide adequate ventilation.

Eye/face protection

Avoid contact with eyes. Large Spillages: Eyewear complying with an approved standard should be worn if a risk assessment indicates eye contact is possible.

Hand protection

No specific hand protection recommended. For users with sensitive skin, it is recommended that suitable protective gloves are worn. The most suitable glove should be chosen in consultation with the glove supplier/manufacturer, who can provide information about the breakthrough time of the glove material.

Other skin and body protection

Appropriate footwear and additional protective clothing complying with an approved standard should be worn if a risk assessment indicates skin contamination is possible.

Hygiene measures

Wash hands thoroughly after handling. Do not eat, drink or smoke when using this product. Wash contaminated clothing before reuse.

Respiratory protection

No specific recommendations. Provide adequate ventilation. Large Spillages: If ventilation is inadequate, suitable respiratory protection must be worn.

Environmental exposure controls

Keep container tightly sealed when not in use. Avoid release to the environment.

9. Physical and Chemical Properties

Information on basic physical and chemical properties

Appearance	Liquid-impregnated wipe.
Color	Colorless.
Odor	Characteristic.
Odor threshold	Not available.
pH	Not available.
Melting point	Not available.
Initial boiling point and range	Not available.

Electrolube IPA Cleaning Wipes x100

Flash point	Not available.
Evaporation rate	Not available.
Evaporation factor	Not available.
Flammability (solid, gas)	Not available.
Upper/lower flammability or explosive limits	Not available.
Other flammability	Not available.
Vapor pressure	Not available.
Vapor density	Not available.
Relative density	Not available.
Bulk density	Not available.
Solubility(ies)	Not available.
Partition coefficient	Not available.
Auto-ignition temperature	Not available.
Decomposition Temperature	Not available.
Viscosity	Not available.
Explosive properties	Not considered to be explosive.
Oxidizing properties	Does not meet the criteria for classification as oxidizing.

10. Stability and reactivity

Reactivity	There are no known reactivity hazards associated with this product.
Stability	Stable at normal ambient temperatures and when used as recommended. Stable under the prescribed storage conditions.
Possibility of hazardous reactions	The following materials may react strongly with the product: Oxidizing agents.
Conditions to avoid	Avoid heat, flames and other sources of ignition. Containers can burst violently or explode when heated, due to excessive pressure build-up. Static electricity and formation of sparks must be prevented.
Materials to avoid	Oxidizing materials. Acids - oxidizing.
Hazardous decomposition products	Does not decompose when used and stored as recommended. Thermal decomposition or combustion products may include the following substances: Harmful gases or vapors.

11. Toxicological information

Information on toxicological effects

Acute toxicity - oral

Notes (oral LD₅₀) Based on available data the classification criteria are not met.

Acute toxicity - dermal

Notes (dermal LD₅₀) Based on available data the classification criteria are not met.

Electrolube IPA Cleaning Wipes x100

Acute toxicity - inhalation

Notes (inhalation LC₅₀) Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Causes serious eye irritation.

Respiratory sensitization

Respiratory sensitization Based on available data the classification criteria are not met.

Skin sensitization

Skin sensitization Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity Based on available data the classification criteria are not met.

IARC carcinogenicity

Contains a substance which may be potentially carcinogenic. IARC Group 3 Not classifiable as to its carcinogenicity to humans.

Reproductive toxicity

Reproductive toxicity - fertility Based on available data the classification criteria are not met.

Reproductive toxicity - development Based on available data the classification criteria are not met.

Specific target organ toxicity - single exposure

STOT - single exposure STOT SE 3 - H336 May cause drowsiness or dizziness.

Target organs Central nervous system

Specific target organ toxicity - repeated exposure

STOT - repeated exposure Not classified as a specific target organ toxicant after repeated exposure.

Aspiration hazard

Aspiration hazard Based on available data the classification criteria are not met.

General information

The severity of the symptoms described will vary dependent on the concentration and the length of exposure.

Inhalation

A single exposure may cause the following adverse effects: Headache. Nausea, vomiting. Central nervous system depression. Drowsiness, dizziness, disorientation, vertigo. Narcotic effect.

Ingestion

No specific symptoms known.

Skin Contact

No specific symptoms known.

Eye contact

Irritating to eyes.

Route of entry

Ingestion Inhalation Skin and/or eye contact

Target Organs

Central nervous system

Propan-2-ol

Electrolube IPA Cleaning Wipes x100

Acute toxicity - dermal

Notes (dermal LD₅₀) LD₅₀ 5840 mg/kg, Oral, Rat REACH dossier information. Based on available data the classification criteria are not met.

Skin corrosion/irritation

Animal data Primary dermal irritation index: 0 REACH dossier information. Based on available data the classification criteria are not met.

Serious eye damage/irritation

Serious eye damage/irritation Dose: 0.1 mL, 1 second, Rabbit Causes serious eye irritation.

Skin sensitization

Skin sensitization Buehler test - Guinea pig: Not sensitizing. REACH dossier information. Based on available data the classification criteria are not met.

Germ cell mutagenicity

Genotoxicity - in vitro Gene mutation: Negative. REACH dossier information. Based on available data the classification criteria are not met.

Genotoxicity - in vivo Chromosome aberration: Negative. REACH dossier information. Based on available data the classification criteria are not met.

Carcinogenicity

Carcinogenicity NOAEL 5000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.

IARC carcinogenicity IARC Group 3 Not classifiable as to its carcinogenicity to humans.

Specific target organ toxicity - single exposure

STOT - single exposure STOT SE 3 - H336 May cause drowsiness or dizziness.

Target organs Central nervous system

Specific target organ toxicity - repeated exposure

STOT - repeated exposure NOAEC 5000 ppm, Inhalation, Rat REACH dossier information. Based on available data the classification criteria are not met.

12. Ecological Information

Ecotoxicity Not regarded as dangerous for the environment. However, large or frequent spills may have hazardous effects on the environment.

Toxicity Based on available data the classification criteria are not met.

Propan-2-ol

Toxicity Aquatic toxicity is unlikely to occur. Based on available data the classification criteria are not met.

Acute toxicity - fish LC₅₀, 96 hours: 10000 mg/l, Pimephales promelas (Fat-head Minnow)

Acute toxicity - aquatic invertebrates LC₅₀, 24 hours: >10000 mg/l, Daphnia magna

Acute toxicity - aquatic plants EC₅₀, 7 days: 1800 mg/l, Scenedesmus quadricauda

Electrolube IPA Cleaning Wipes x100

Persistence and degradability

Persistence and degradability The degradability of the product is not known.

Propan-2-ol

Persistence and degradability The substance is readily biodegradable.

Biodegradation Water - Degradation 53%: 5 days

Biological oxygen demand 1.19-1.72 g O₂/g substance

Chemical oxygen demand 2.23 g O₂/g substance

Bioaccumulative potential

Bio-Accumulative Potential No data available on bioaccumulation.

Partition coefficient Not available.

Propan-2-ol

Bio-Accumulative Potential Bioaccumulation is unlikely.

Mobility in soil

Mobility No data available.

Propan-2-ol

Mobility The product is soluble in water.

Other adverse effects

Other adverse effects None known.

13. Disposal considerations

Waste treatment methods

General information The generation of waste should be minimized or avoided wherever possible. Reuse or recycle products wherever possible. This material and its container must be disposed of in a safe way. When handling waste, the safety precautions applying to handling of the product should be considered. Care should be taken when handling emptied containers that have not been thoroughly cleaned or rinsed out. Empty containers or liners may retain some product residues and hence be potentially hazardous.

Disposal methods Dispose of waste to licensed waste disposal site in accordance with the requirements of the local Waste Disposal Authority.

14. Transport information

UN Number

UN No. (TDG) 3175

UN No. (IMDG) 3175

UN No. (ICAO) 3175

UN No. (DOT) UN3175

UN proper shipping name

Electrolube IPA Cleaning Wipes x100

Proper shipping name (TDG) SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S.

Proper shipping name (IMDG) SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S.

Proper shipping name (ICAO) SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S.

Proper shipping name (DOT) SOLIDS CONTAINING FLAMMABLE LIQUID, N.O.S.

Transport hazard class(es)

DOT hazard class 4.1

DOT hazard label 4.1

TDG class 4.1

TDG label(s) 4.1

IMDG Class 4.1

ICAO class/division 4.1

Transport labels



DOT transport labels



Packing group

TDG Packing Group II

IMDG packing group II

ICAO packing group II

DOT packing group II

Environmental hazards

Environmentally Hazardous Substance

No.

Special precautions for user

EmS F-A, S-I

15. Regulatory information

US Federal Regulations

SARA Section 302 Extremely Hazardous Substances Tier II Threshold Planning Quantities

None of the ingredients are listed or exempt.

CERCLA/Superfund, Hazardous Substances/Reportable Quantities (EPA)

None of the ingredients are listed or exempt.

SARA Extremely Hazardous Substances EPCRA Reportable Quantities

None of the ingredients are listed or exempt.

Electrolube IPA Cleaning Wipes x100

SARA 313 Emission Reporting

None of the ingredients are listed or exempt.

CAA Accidental Release Prevention

None of the ingredients are listed or exempt.

FDA - Essential Chemical

None of the ingredients are listed or exempt.

FDA - Precursor Chemical

None of the ingredients are listed or exempt.

SARA (311/312) Hazard Categories

None of the ingredients are listed or exempt.

OSHA Highly Hazardous Chemicals

None of the ingredients are listed or exempt.

US State Regulations

California Proposition 65 Carcinogens and Reproductive Toxins

None of the ingredients are listed or exempt.

California Air Toxics "Hot Spots" (A-I)

The following ingredients are listed or exempt:

California Air Toxics "Hot Spots" (A-II)

None of the ingredients are listed or exempt.

California Directors List of Hazardous Substances

The following ingredients are listed or exempt:

Massachusetts "Right To Know" List

The following ingredients are listed or exempt:

Rhode Island "Right To Know" List

The following ingredients are listed or exempt:

Minnesota "Right To Know" List

The following ingredients are listed or exempt:

New Jersey "Right To Know" List

The following ingredients are listed or exempt:

Pennsylvania "Right To Know" List

The following ingredients are listed or exempt:

Inventories

US - TSCA

The following ingredients are listed or exempt:

US - TSCA 12(b) Export Notification

The following ingredients are listed or exempt:

16. Other information

Training advice

Read and follow manufacturer's recommendations.

Electrolube IPA Cleaning Wipes x100

Issued by	Toni Ashford
Revision date	5/24/2016
Revision	0
SDS No.	357
Hazard statements in full	H225 Highly flammable liquid and vapor. H319 Causes serious eye irritation. H336 May cause drowsiness or dizziness.

This information relates only to the specific material designated and may not be valid for such material used in combination with any other materials or in any process. Such information is, to the best of the company's knowledge and belief, accurate and reliable as of the date indicated. However, no warranty, guarantee or representation is made to its accuracy, reliability or completeness. It is the user's responsibility to satisfy himself as to the suitability of such information for his own particular use.