



Main

Range of product	Preventa XY2
Product or component type	Simple rope pull switch
Device short name	XY2CD
Housing colour	Blue
Overvoltage category	Class I conforming to EN/IEC 61140 Class I conforming to NF C 20-030

Complementary

Trigger cable maximum length	6 m
Body material	Zamak
Head material	Plastic
[Us] rated supply voltage	240 V
Contacts type and composition	1 NC + 1 NO
Contact operation	Snap action
Operating force	237 daN
Pulling force	36 daN
Cable entry number	3 3 entries tapped for Pg 13.5 cable gland for Pg 13.5
Mechanical durability	1500000 cycles
[Ie] rated operational current	3 A at 240 V AC-15, A300 conforming to EN/IEC 60947-5-1 appendix A 0.27 A at 250 V DC-13, Q300 conforming to EN/IEC 60947-5-1 appendix A
[Ithe] conventional enclosed thermal current	10 A
[Ui] rated insulation voltage	300 V (degree of pollution: conforming to UL 508 300 V (degree of pollution: conforming to CSA C22.2 No 14 400 V (degree of pollution: 3) conforming to EN/IEC 60947-1

Environment

Product certifications	CCC CE
------------------------	-----------

Ambient air temperature for operation	-20...70 °C
IP degree of protection	IP66 for conforming to IEC 60529

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0852 - Schneider Electric declaration of conformity Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold Reference not containing SVHC above the threshold
Product end of life instructions	Need no specific recycling operations