

148-90037

Article Number: 148-90037

Description: HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 3-Port, (PC), Orange, 100/pkg



Base Data	
Local Order Number	HCPM-3
Type	HCPM-3
Color	Clear (CL) Orange (OG)
Features and benefits	<ul style="list-style-type: none"> • Double-spring technology for safe, secure and reliable connections. • Smaller footprint fits in tight spaces. • Low insertion force makes installation of solid or stranded copper wire fast and easy. • Color coded for easy identification of size. • Each port accepts multiple wire diameters for flexible applications. • Accepts 12–22 AWG solid wire and 14–22 AWG stranded wire.
Quantity Per	box
Brand Family	HelaCon
Product Description	HelaCon Plus Mini Wire Connectors replace traditional twist-on wire connectors. They provide faster, easier and more reliable connection and distribution of cable and conductors in electrical installation applications. Mini connectors have a compact footprint and can be applied tool-free using convenient, push-in simplicity. Internal double-spring technology is approved for solid and stranded wires.
GLOBAL PART NAME (auto set)	HCPM-3-PC-CL/OG
Voltage Rating (cULus)	600 V
Voltage Rating (VDE)	450 V
Short Description	HelaCon Plus Mini, Push-In Style Wire Connector, Double Spring, 3-Port, (PC), Orange, 100/pkg
Product Dimensions	
Length L (Imperial)	0.65"
Length L (Metric)	16.5mm
Max Current	24A
Max Voltage	600V
Number of Conductors	3
Width W (Imperial)	0.59"
Width W (Metric)	15.1mm

148-90037



Product Dimensions	Height H (Imperial)	0.30"
	Height H (Metric)	7.70mm
	Depth D (metric)	16.5mm
	Depth D (imperial)	0.65"
Material and Specifications		
	Material	Polycarbonate (PC)
	Material Shortcut	PC
	Flammability	UL 94 V0
	Halogenfree	Yes
	Operating Temperature	-22°F to +185°F (-30°C to +85°C)
	REACH Compliant (Article 33)	Yes
	ROHS Compliant	Yes
	UL Listed (US and Canada)	Yes
	UL Recognized (US and Canada)	Yes
Logistic and Packaging		
	Package Quantity (Imperial)	100
	Package Quantity (Metric)	100Pieces