

# 97 53 08

## Self-Adjusting Crimping Pliers for End Sleeves (ferrules) with front loading




PATENTED



- For crimping end sleeves (ferrules) according to DIN 46228 parts 1 + 4
- Self-adjusting adaptation to the desired end sleeve (ferrule) size: no wrong crimps caused by using the wrong die
- Front loading of the end sleeves (ferrules) into the tool
- Repetitive, high crimping quality due to integral lock (self-releasing mechanism)
- Crimping pressure has been set precisely (calibrated) in the factory, re-adjustable
- Optimum transmission of force thanks to toggle lever for fatigue-reduced operation
- Handy shape and low weight provide high operation comfort
- Chrome vanadium electric steel in special quality, oil-hardened
- Compression from 0.08 - 10.0 mm<sup>2</sup> in one profile
- End sleeves (ferrules) up to 2.5 mm<sup>2</sup> can also be loaded parallelly from the side
- Suitable in particular for all twin end sleeves (ferrules) up to 2 x 4 mm<sup>2</sup> or 2 x AWG 10

The crimping pliers for end sleeves (ferrules) with three great advantages for the user: - Automatic self-adjustment to the end sleeve (ferrule) used: this allows the specialist to work with less strain and enables secure, reliable and quick crimping. - Range of applications also for large cross-sections: square crimping 0.08 to 10.0 + 16.0 mm<sup>2</sup> - Front loading: very helpful under difficult working conditions in confined areas.


<b>Article No.</b>	97 53 08
<b>EAN</b>	4003773040187
<b>Pliers</b>	burnished
<b>Handles</b>	with multi-component grips
<b>Applications</b>	End Sleeves (ferrules)
<b>Capacity in square millimetres mm<sup>2</sup></b>	0,08 - 10
<b>Number of crimping positions</b>	1
<b>AWG</b>	28 - 7
<b>Length mm</b>	190
<b>Net weight g</b>	477



Front loading of end sleeves (ferrules) e.g. in switchboards



Square compression



97 53 08: lateral loading of end sleeves (ferrules) up to 2.5 mm<sup>2</sup> parallelly from the side e.g. in confined areas

technical change and errors excepted



### Spare Parts

<b>Article No.</b>	<b>EAN</b>	
97 59 30	4003773053965	Extension spring for 97 53 4/5/8/9/14

97 59 31	4003773053972	Extension spring for 97 53 4/5/8/9/14
97 59 32	4003773053989	Circlips for model 97 53 for 97 53 xx