


# 77 12 115 ESD

## Electronics Diagonal Cutter ESD



- For fine cutting work, e.g. in electronics and fine mechanics
- Electrically discharging handles - dissipative
- Sturdy, zero-backlash box joint
- Low-friction double spring for gentle and even opening
- The mirror polish together with a fine film of oil offer effective rust protection - no circuit faults caused by peeling chrome from plated tools
- Cutting edges additionally induction hardened
- With two-colour dual component grips, black/grey
- High-grade special tool steel, forged, multi stage oil-hardened
- Round head, with bevel and lead catcher - no uncontrolled loss of cut wire ends
- Cutting edge hardness approx. 62 HRC





### ESD pliers (electrostatic discharge)

electrostatic energy is discharged through the handles in a gradual and controlled manner

which protects components endangered by electrostatic discharge

in accordance with applicable standards, e.g. IEC TR 61 340-5, DIN EN 61 340-5, SP Method 2472

<b>Article No.</b>	77 12 115 ESD
<b>EAN</b>	4003773025108
<b>Head</b>	mirror polished
<b>Handles</b>	with multi-component grips
<b>Style</b>	1
<b>Cutting capacities medium hard wire (diameter) Ø mm</b>	1,2
<b>Cutting capacities hard wire (diameter) Ø mm</b>	0,6
<b>Cutting capacities soft wire (diameter) Ø mm</b>	0,3 - 1,6
<b>B mm</b>	14,0
<b>D mm</b>	7,5
<b>A mm</b>	11,0
<b>Length mm</b>	115
<b>Net weight g</b>	80



technical change and errors excepted

