4503 intelligent multimeter Full Talk and Listen via built-in IEEE488 and RS232 Interfaces



580-448

- Autoranging
- 0.03% basic accuracy
- True RMS
- Auto calibration
- Reading 3/sec
- 41/2 digit LED

- 1000V DC, 750V AC
- 10A AC & DC
- 20MΩ Resistance
- Null, Hold, Continuity,
 Filter, Diode Test, dB, Data
 Logger, % Deviation,
 Ax+b, Rel

Black*****Star



Designed and manufactured in Britain

4503 INTELLIGENT MULTIMETER

DC VOLTAGE

2000	200V	20V	27	.2 ⁻	Range
100mV	10mV	1mV	100uV	10uV	Resolution
±0.05% rdg ±0.01% ts	±0.03% rdg ±0.01% is	±0.03% rdg ±0.01% ts	±0.03% rdg ±0.01% ts	±0.03% rdg ±0.01% fs	Accuracy

Maximum permissible input voltage: 1000V DC (.2V range 1000V DC 5 sec.)

Input impedance: 10M Ω ± 0.25%

Normal mode rejection ratio: 60dB @ 50Hz

Common mode rejection ratio: 100dB @ 50Hz with 1k Ω imbalance

Range 2mA 200mA 10A Resolutio 100nA ±1% rdg ±0.02% fs ±0.15% rdg ±0.02%fs 10uV/count < 15uV/count 0.5A (fused) 0.5A (fused) Max. Input 20A (10 sec.

AC VOLTAGE TRUE RMS

.2V 2V 20V 200V 2000V	Range
10uV 100uV 1mV 10mV 100mV	Resolution
±0.5% rdg ±0.1% fs ±0.5% rdg ±0.1% fs ±0.5% rdg ±0.1% fs ±0.5% rdg ±0.1% fs ±10.5% rdg ±0.1% fs	45Hz-400Hz
±1% rdg ±0.1% fs ±1% rdg ±0.1% fs ±2% rdg ±0.1% fs ±2% rdg ±0.1% fs ±2% rdg ±0.1% fs ±7% rdg ±0.1% fs	Accuracy (>10% fs)
±3% rdg ±0.1% fs ±5% rdg ±0.1% fs ±5% rdg ±0.1% fs ±5% rdg ±0.1% fs ±5% rdg ±0.1% fs	5kHz-20kHz

Accuracy for .2V range at low levels:

Level 10mV 3mV 1mV	
Max. Frequency for < 1% Error 6kHz 1kHz 250Hz	
Max. Frequency for <10% Erroi 15kHz 8kHz 2kHz	

Common mode rejection ratio: 40 dB @ 50Hz with 1k (2 imbalance Maximum permissible input voltage: 750V AC (.2V range 1000V pk 10 sec.), 10⁶VxHz

Crest Factor: < 5 @ fs for < 3% increase in error

AC CURRENT TRUE RMS

	200mA 10uA		Range Resolution	
± 1.5% rdg + 0.1% fs	$\pm 0.5\%$ rdg + 0.1% fs		_	AC CONN
<15uV/count			Voltage Burden	AC CONNEIL INCL MAIN
20A (10 Sec.)	0.5A (fused)	0.5A (fused)	Max. Input	•

Crest Factor: <2 @ fs for <2% increase in error

RESISTANCE

Range	Resolution	Accuracy	Excitation Current
2 C	10m Ω	$\pm 0.1\%$ rdg $\pm 0.02\%$ fs	0.5mA
3,0	100m Ω	$\pm 0.1\%$ rdg $\pm 0.02\%$ fs	0.1mA
30.00	10	$\pm 0.1\%$ rdg $\pm 0.02\%$ fs	10uA
3000	10 O	±0.15% rda ±0.02% fs	1uA
2000	100 10	±0.3% rdg ±0.03% fs	100nA
20M 12	1 k Ω	±1% rdg ±0.04% fs	100nA
	: :: 1. :		

Maximum permissible input voltage: 3/0V pk)

AUTORANGING CAPABILITY

Autoranging on all voltage and resistance ranges and 2mA/200mA (AC and DC) current ranges

OTHER FUNCTIONS

HOLD CONTINUITY % DEVIATION DIODE TEST Ax+b DATA LOGGER FILTER Allows user to make relative measurements Deviation in % from user selected nominal reference value Averaging noise reduction filter Scale and offset measurement. User selected scale factor and offset 100 reading logger. User settable sample interval Calculation error ± 0.02 dB. User selectable reference impedance Diode forward voltage measured with excitation current 1mA, 1Vfs Audible continuity test Removes residual offset on DC voltage and resistance ranges

CALIBRATION

Closed case, fully automatic, via IEEE-488 or RS232 (except AC frequency response)

Full IEEE-488/GP-1B talker/listener. Also RS232. Interfaces built-in INTERFACING

IEEE-488/GP-IB SUBSET IMPLEMENTION

 9 11				SH1 AH1 TE0 TE0 LE0 LE0 PP.2	Source handshake — complete capability Acceptor handshake — complete capability Acceptor handshake — complete capability Basic talker + serial poll + talk only mode + unaddress if MLA Extended talker — no capability Basic listener + unaddress if MTA Extended listener — no capability Service request — complete capability Remote/local — complete capability Parallel poll — remote configuration
•				 •	David received to the second little

CONTROLLABLE FUNCTIONS

CO DTO

Not a controller

GP-IB service request is initiated. Serial and parallel polling are supported. Instrument status, error messages and RS232 interfaces. The string terminator may be selected, and the conditions under which an IEEE-488/ All ranges and functions (except 10A AC and DC) are settable and controllable via the built-in IEEE-488/GP-IB and readings may be requested.

Accuracy Temperature Coefficient: Typically < 0.1 x applicable accuracy spec. per °C (10°C to 18°C, The accuracy specifications apply over a temperature of 18°C to 22°C typically for 1 year

22°C to 35°C)

Maximum Common Mode Input Voltage: 500V DC or peak AC.

Mains Input Voltage: 220/240V (110V set internally) \pm 10%

Display: 13mm LED, 6 digit

Polarity: Automatic

Scale Length: 4 1/2 digit, 20999 counts max.

Operating Temperature Range: 5°C to 40°C, 10% to 80% RH. Supplied Accessories: Built-in IEEE-488/GP-IB and RS232 Interfaces, Instruction Manual, Spare Fuse, Test Reading Rate: 3 per sec. Zero: automatic

Optional Accessories: Service Manual, Carry Case

Size: 219mm x 240mm x 98mm (product only) 300mm x 300mm x 116mm (packed)

Black Star reserve the right to after specifications without notice

Weight: 2.3kg (product only) 2.6kg (packed)

Designed and Manufactured by:

BLACK STAR LTD. 4 Harding Way Cambs. PE17 4WR. England St. Ives, Huntingdon

Telex: 32762 Fax: (0480) 495172

Tel: (0480) 62440

Available from: