



Product information Configurable Industrial Security-Router - EagleOne-0200T1T1SDDUY0000HHE05.3.

Industrial Ethernet:Industrial Firewall System:EAGLE One:Configurable Industrial Security-Router	
https://www.e-catalog.beldensolutions.com/443/link/57078-24455-49853-401129-400975/en/EagleOne-0200T1T1SDDUY0000HHE05.3./uistate	
Name	Configurable Industrial Security-Router
	
	Industrial firewall and security router with extensive Layer 2 and Layer 3 redundancy features, DIN rail mounted, fanless design.
Delivery informations	
Availability	available
Product description	
Description	Industrial firewall and security router with extensive Layer 2 and Layer 3 redundancy features, DIN rail mounted, fanless design.
Port type and quantity	2 ports in total, Ports Fast Ethernet: 2 x 10/100 Mbit/s
Type	EagleOne-0200T1T1SDDUY0000HHE05.3.
Order No.	942 103-001
More Interfaces	
Power supply/signaling contact	1 x plug-in terminal block, 6-pin
Digital Input	1 x plug-in terminal block, 2-pin
V.24 interface	1 x RJ11 socket
USB interface	1 x USB to connect the AutoConfiguration Adapter ACA21-USB EEC
Network size - length of cable	
Twisted pair (TP)	0 m ... 100 m
Network size - cascading	
Line - / star topology	any
Power requirements	
Operating voltage	12/24/48 VDC/24 VAC (redundant)
Power consumption	6.9 W
Software	
Stateful inspection firewall	Firewall rules (incoming/outgoing, management), DoS prevention, MAC filter, user firewall for external activation of FW rules
Management	SNMPv3, SSH2/SFTP, HTTPS, V.24 CLI, central user management (RADIUS), SSH1, SNMPv1/2, HiDiscovery, Industrial HiVision, HiView
Multipoint VPN	Point to point, point to multipoint, remote enable/disable or via digital input, IPsec, IKEv1/v2, 3DES, AES (-128, -192, -256), Pre-Shared Key, X.509v3 certificates, MD5, SHA-1, NAT-T
Diagnostics	LLDP, LEDs (status, VPN, redundancy, link status, data, ACA), signal contact, logfile, syslog, configuration check
Configuration	Web based GUI, SNMPv3, CLI, Automatic configuration roll-back, text based configuration file, offline configuration, HiView
Security	HTTPS, SSHv2, SFTP, SNMPv3, Management VLAN, Role based Access
Routing	Static routing, multinetting, IP masquerading, 1-to-1 NAT, port forwarding.
Redundancy functions	Use in redundant networks/ring coupling, firewall redundancy (layer 4)
Time synchronisation	NTP/SNTP
Miscellaneous	DHCP Server/Client, DHCP Relay/Option 82, DynDNS, PPP, PPPoE, VLAN-Support , packet capture (pcap Format)
Ambient conditions	
Operating temperature	0 °C ... 60 °C
Storage/transport temperature	-40 °C ... 85 °C
Relative humidity (non-condensing)	10 % ... 95 %
Mechanical construction	
Dimensions (W x H x D)	60 mm x 145 mm x 125 mm
Mounting	DIN Rail
Weight	660 g
Protection class	IP20
Approvals	
Basis Standard	CE, FCC, C-Tick, EN61131, EN 60950-1 ,



HIRSCHMANN

A BELDEN BRAND

Industrial Ethernet:Industrial Firewall System:EAGLE One:Configurable Industrial Security-Router

<https://www.e-catalog.beldensolutions.com:443/link/57078-24455-49853-401129-400975/en/EagleOne-0200T1T1SDDUY0000HHE05.3./ulstate>

Safety of information technology equipment	cUL 508
Shipbuilding	Germanischer Lloyd
Scope of delivery and accessories	
Scope of delivery	Device, terminal blocks, operating instructions, manual on CD
Accessories to order separately	Rail power supply RPS 30, RPS 80 EEC, RPS 120 EEC, terminal cable, network management Industrial HiVision, auto-configuration adapter ACA21-USB EEC, 19" installation frame

For more information please contact:

Hirschmann Automation and Control GmbH

Stuttgarter Strasse 45-51

72654 Neckartenzlingen

Germany

Phone: +49 7127/14-1809

E-Mail: inet-sales@belden.com

The information published in the websites has been compiled as carefully as possible. It is subject to alteration without notice in technical as well as in price-related/commercial respect. The complete information and data were available on user documentation. Mandatory information can only be obtained by a concrete query.