



Main

Range of product	OsiSense XG
Product or component type	Electronic tag
RFID electronic tag name	XGHB
RFID frequency	13.56 MHz
Design	Disc
Memory capacity	2 kB
Associated smart antenna	XGCS
[Sn] nominal sensing distance	42 mm with XGCS49 + field expander XGFEC540 48 mm with XGCS49 65 mm with XGCS89 80 mm with XGCS49 + field expander XGFEC2525 65 mm with XGCS85
Outer dimension	Ø 30 x 3 mm
Quantity per set	Set of 5
Read time	7 + 2 x (number of 16-bit words) ms
Write time	7 + 2.4 x (number of 16-bit words) ms
IP degree of protection	IP68
Fixing mode	By screws

Complementary

Memory type	FeRAM
Memory operation	Read/Write
Number of read cycles	1000000000
Number of write cycles	1000000000 at -25...70 °C
Maximum linear speed with "auto read/write function"	With XGCS49 (read a serial number) With XGCS49 (read a word) With XGCS49 (read or write 10 words) With XGCS89 (read a serial number) With XGCS89 (read a word) With XGCS89 (read or write 10 words) With XGCS85 (read a serial number) With XGCS85 (read a word) With XGCS85 (read or write 10 words)
Data retention time	10 yr
Material	PPA (polyphthalamide)
Product weight	0.005 kg

Environment

Standards	ISO 15693
Ambient air temperature for operation	-25...70 °C
Ambient air temperature for storage	-40...85 °C
Vibration resistance	2 mm (f = 5...29.5 Hz) conforming to EN 60068-2-6 7 gn (f = 29.5...150 Hz) conforming to EN 60068-2-6
Shock resistance	30 gn for 11 ms conforming to EN 60068-2-27
IK degree of protection	IK02 conforming to EN 50102

Offer Sustainability

Sustainable offer status	Not Green Premium product
--------------------------	---------------------------