

XGHB90E340

RFID electronic tag - 13.56 MHz - ISO badge
54 x 85.5 x 1 - 256 Bytes



Main

Range of product	OsiSense XG
Product or component type	Electronic tag
RFID electronic tag name	XGHB
RFID frequency	13.56 MHz
Design	ISO badge
Memory capacity	256 B
Associated smart antenna	XGCS
[Sn] nominal sensing distance	100 mm with XGCS89 150 mm with XGCS49 + field expander XGFEC2525 70 mm with XGCS49 90 mm with XGCS49 + field expander XGFEC540 100 mm with XGCS85
Outer dimension	54 x 85.5 x 1 mm
Quantity per set	Set of 10
Read time	12 + 0.825 x (number of 16-bit words) ms
Write time	20 + 11.8 x (number of 16-bit words) ms
IP degree of protection	IP65

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

Complementary

Memory type	EEPROM
Memory operation	Read/Write
Number of read cycles	Unlimited
Number of write cycles	100000 at -25...50 °C 2500000 at 30 °C
Maximum linear speed with "auto read/write function"	With XGCS49 (read or write 10 words) With XGCS49 (read a serial number) With XGCS49 (read a word) With XGCS89 (read a serial number) With XGCS89 (read a word) With XGCS89 (read or write 10 words) With XGCS85 (read a serial number) With XGCS85 (read a word) With XGCS85 (read or write 10 words)
Data retention time	10 yr
Material	PVC (polyvinyl chloride)
Product weight	0.005 kg

Environment

Standards	ISO 15693
Ambient air temperature for operation	-25...50 °C
Ambient air temperature for storage	-40...55 °C
Vibration resistance	2 mm (f = 5...29.5 Hz) conforming to EN 60068-2-6 7 gn (f = 29.5...150 Hz) conforming to EN 60068-2-6
Shock resistance	30 gn for 11 ms conforming to EN 60068-2-27
IK degree of protection	IK02 conforming to EN 50102

Offer Sustainability

Sustainable offer status	Green Premium product
RoHS (date code: YYWW)	Compliant - since 0727 - Schneider Electric declaration of conformity
REACH	Reference not containing SVHC above the threshold
Product environmental profile	Available Download Product Environmental
Product end of life instructions	Available Download End Of Life Manual

Dimensions

mm
in.

