

0 611 910 000 – GBH 18V-26 F

Material number	0 611 910 000	0 611 910 072	0 611 910 074
EAN	3165140807937	3165140807968	3165140821322
2 x 6.0 Ah Li-Ion battery 1 600 A00 4ZN			✓
2 x battery GBA 18V 6.0Ah 1 600 A00 4ZN		✓	
Auxiliary handle 2 602 025 141	✓	✓	✓
Cardboard box	✓		
Depth stop 210 mm 1 613 001 010	✓	✓	✓
GAL 1880 CV quick charger 1 600 A00 B8G			✓
GDE 18V-16 Professional dust extraction system 1 600 A00 51M			✓
L-BOXX 136 1 600 A00 1RR		✓	
L-BOXX 238 1 600 A00 1RS			✓
L-BOXX inlay		✓	✓
Machine cloth	✓	✓	✓
Quick change chuck 2 608 572 212	✓	✓	✓
Quick charger GAL 1880 CV 1 600 A00 B8G		✓	
SDS-plus quick-change chuck 2 608 572 213	✓	✓	✓
Weight incl. battery	3,6 kg	3,6 kg	3,6 kg



Technical data

Technical data

Max. impact energy	2.6 J
Impact rate at rated speed	0 – 4.350 bpm
Rated speed	0 – 890 rpm
Battery voltage	18 V
Works with battery capacity	6,0 Ah
Length	378,0 mm
Height	225,0 mm
Bit holder	SDS-plus

Drilling range

Drilling dia. in concrete with hammer drill bits	4 – 26 mm
Opt. app. range in concrete with hammer drill bits	8 – 16 mm
Max. drilling diameter in steel	13 mm
Max. drilling diameter in wood	30 mm

Noise/vibration information

Sound pressure level	91 dB(A)
Sound power level	102 dB(A)
Uncertainty K	3 dB



Sales information

Positioning

- More power, more comfort and less dust

User benefit

- 50% more power with the impact force of a corded tool for fast, versatile use (compared to predecessor GBH 18 V-EC)
- Increased user protection with KickBack Control (KBC) and better control with Electronic Precision Control (EPC)
- Drill without dust thanks to the new integrated, optional GDE 18V-16 dust extraction system

Other features

- Brushless EC motor: compact, dust-protected, lightweight and absolutely maintenance-free
- Vibration Control: decoupled handle for low user fatigue
- Long runtime: up to 216 holes in concrete with only one battery charge (6 x 40 mm)
- LED worklight: an optimum view of the work position
- Ergonomic design: best horizontal power transfer to the hole
- Electronic Cell Protection (ECP): protects the battery against overloading, overheating and deep discharge
- Innovative COOLPACK batteries: ensure optimum heat dissipation and therefore increase lifetime by up to 100% (cf. Li-Ion batteries without COOLPACK)
- No memory effect: the battery can be charged regardless of the charging state at any time, without damaging the cells
- Fastest charging time: 80% of the battery is charged after 35 mins
- Quick-change chuck for fast changes between drilling with impact in concrete and drilling without impact in wood and metal