

KEMET Part Number: C1812C394G3JACTU
(C1812C394G3JAC7800)

SMD Comm U2J, Ceramic, 0.39 uF, 2%, 25 V, U2J, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 1812



Dimensions

| | |
|----------|-----------------|
| L | 4.5mm +/-0.3mm |
| W | 3.2mm +/-0.3mm |
| T | 1.4mm +/-0.15mm |
| B | 0.6mm +/-0.35mm |

Packaging Specifications

| | |
|----------------------------|--------------------------|
| Packaging: | T&R, 180mm, Plastic Tape |
| Packaging Quantity: | 1000 |

General Information

| | |
|-----------------------|--|
| Supplier: | KEMET |
| Series: | SMD Comm U2J |
| Style: | SMD Chip |
| Description: | SMD, MLCC, Ultra-Stable, Low Loss, Class I |
| Features: | Ultra-Stable, Low Loss, Class I |
| RoHS: | Yes |
| Termination: | Tin |
| Marking: | No |
| Failure Rate: | N/A |
| Miscellaneous: | Note: Referee time for U2J dielectric for this part number is 1000 hours |
| Chip Size: | 1812 |

Specifications

| | |
|---|-----------------------|
| Capacitance: | 0.39 uF |
| Capacitance Tolerance: | 2% |
| Voltage DC: | 25 VDC |
| Dielectric Withstanding Voltage: | 62.5 V |
| Temperature Range: | -55/+125C |
| Temperature Coefficient: | U2J |
| Dissipation Factor: | 0.1% 1kHz 25C |
| Aging Rate: | 0.1% Loss/Decade Hour |
| Insulation Resistance: | 2.564 GOhms |