



## Safety Data Sheet according to Regulation (EC) No 1907/2006

Page 1 of 10

5368 BLACK 20LT M/L

SDS No. : 164824  
V004.0

Revision: 05.09.2016

printing date: 16.01.2018

Replaces version from: 18.12.2015

### SECTION 1: Identification of the substance/mixture and of the company/undertaking

#### 1.1. Product identifier

5368 BLACK 20LT M/L

#### 1.2. Relevant identified uses of the substance or mixture and uses advised against

Intended use:  
Silicone sealant

#### 1.3. Details of the supplier of the safety data sheet

Henkel Ltd  
Wood Lane End  
HP2 4RQ Hemel Hempstead

Great Britain

Phone: +44 1442 278000

Fax-no.: +44 1442 278071

ua-productsafety.uk@uk.henkel.com

#### 1.4. Emergency telephone number

24 Hours Emergency Tel: +44 (0)1442 278497

### SECTION 2: Hazards identification

#### 2.1. Classification of the substance or mixture

##### Classification (CLP):

Skin irritation Category 2

H315 Causes skin irritation.

Serious eye irritation Category 2

H319 Causes serious eye irritation.

#### 2.2. Label elements

##### Label elements (CLP):

Hazard pictogram:



Signal word: **Warning**

Hazard statement: **H315 Causes skin irritation.**  
**H319 Causes serious eye irritation.**

**Precautionary statement:** P302+P352 IF ON SKIN: Wash with plenty of soap and water.  
P337+P313 If eye irritation persists: Get medical advice/attention.

**2.3. Other hazards**  
None if used properly.

### SECTION 3: Composition/information on ingredients

#### 3.2. Mixtures

**General chemical description:**  
Acetoxy curing silicone

**Declaration of the ingredients according to CLP (EC) No 1272/2008:**

Hazardous components CAS-No.	EC Number REACH-Reg No.	content	Classification
Methyltriacetoxysilane 4253-34-3	224-221-9 01-2119962266-32	1- < 3 %	Acute Tox. 4; Oral H302 Skin Corr. 1B H314

For full text of the H - statements and other abbreviations see section 16 "Other information".  
Substances without classification may have community workplace exposure limits available.

### SECTION 4: First aid measures

#### 4.1. Description of first aid measures

**Inhalation:**  
Move to fresh air. If symptoms persist, seek medical advice.

**Skin contact:**  
Rinse with running water and soap.  
Obtain medical attention if irritation persists.

**Eye contact:**  
Rinse immediately with plenty of running water (for 10 minutes), seek medical attention from a specialist.

**Ingestion:**  
Rinse mouth, drink 1-2 glasses of water, do not induce vomiting, consult a doctor.

#### 4.2. Most important symptoms and effects, both acute and delayed

SKIN: Redness, inflammation.

SKIN: Rash, Urticaria.

EYE: Irritation, conjunctivitis.

#### 4.3. Indication of any immediate medical attention and special treatment needed

See section: Description of first aid measures

### SECTION 5: Firefighting measures

#### 5.1. Extinguishing media

**Suitable extinguishing media:**

Carbon dioxide, foam, powder

Fine water spray

**Extinguishing media which must not be used for safety reasons:**

High pressure waterjet

**5.2. Special hazards arising from the substance or mixture**

Do not expose to direct heat.

In the event of a fire, carbon monoxide (CO), carbon dioxide (CO<sub>2</sub>) and nitrogen oxides (NO<sub>x</sub>) can be released.  
carbon oxides.

Silica fume

Formaldehyde

**5.3. Advice for firefighters**

Wear self-contained breathing apparatus and full protective clothing, such as turn-out gear.

**Additional information:**

In case of fire, keep containers cool with water spray.

## SECTION 6: Accidental release measures

**6.1. Personal precautions, protective equipment and emergency procedures**

Avoid contact with skin and eyes.

Ensure adequate ventilation.

Wear protective equipment.

**6.2. Environmental precautions**

Do not empty into drains / surface water / ground water.

**6.3. Methods and material for containment and cleaning up**

For small spills wipe up with paper towel and place in container for disposal.

For large spills absorb onto inert absorbent material and place in sealed container for disposal.

**6.4. Reference to other sections**

See advice in section 8

## SECTION 7: Handling and storage

**7.1. Precautions for safe handling**

Avoid skin and eye contact.

See advice in section 8

Hygiene measures:

Wash hands before work breaks and after finishing work.

Do not eat, drink or smoke while working.

Good industrial hygiene practices should be observed.

**7.2. Conditions for safe storage, including any incompatibilities**

Store in a cool, well-ventilated place.

Never allow product to get in contact with water during storage

**7.3. Specific end use(s)**

Silicone sealant

**SECTION 8: Exposure controls/personal protection****8.1. Control parameters****Occupational Exposure Limits**Valid for  
Great Britain

None

**Occupational Exposure Limits**Valid for  
Ireland

None

**Predicted No-Effect Concentration (PNEC):**

Name on list	Environmental Compartment	Exposure period	Value				Remarks
			mg/l	ppm	mg/kg	others	
Methylsilanetriyl triacetate 4253-34-3	aqua (freshwater)					1,0 mg/L	
Methylsilanetriyl triacetate 4253-34-3	aqua (marine water)					0,1 mg/L	
Methylsilanetriyl triacetate 4253-34-3	aqua (intermittent releases)					10 mg/L	
Methylsilanetriyl triacetate 4253-34-3	sediment (freshwater)				0,80 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	sediment (marine water)				0,08 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	soil				0,13 mg/kg		
Methylsilanetriyl triacetate 4253-34-3	sewage treatment plant (STP)					> 10 mg/L	

**Derived No-Effect Level (DNEL):**

Name on list	Application Area	Route of Exposure	Health Effect	Exposure Time	Value	Remarks
Methylsilanetriyl triacetate 4253-34-3	Workers	inhalation	Long term exposure - systemic effects		25 mg/m <sup>3</sup>	
Methylsilanetriyl triacetate 4253-34-3	Workers	inhalation	Acute/short term exposure - systemic effects		25 mg/m <sup>3</sup>	
Methylsilanetriyl triacetate 4253-34-3	Workers	dermal	Long term exposure - systemic effects		14,5 mg/kg bw/day	
Methylsilanetriyl triacetate 4253-34-3	Workers	dermal	Acute/short term exposure - systemic effects		14,5 mg/kg bw/day	
Methylsilanetriyl triacetate 4253-34-3	General population	inhalation	Long term exposure - local effects		5,1 mg/m <sup>3</sup>	
Methylsilanetriyl triacetate 4253-34-3	General population	inhalation	Acute/short term exposure - local effects		5,1 mg/m <sup>3</sup>	
Methylsilanetriyl triacetate 4253-34-3	General population	dermal	Long term exposure - systemic effects		7,2 mg/kg bw/day	
Methylsilanetriyl triacetate 4253-34-3	General population	dermal	Acute/short term exposure - systemic effects		7,2 mg/kg bw/day	
Methylsilanetriyl triacetate 4253-34-3	General population	oral	Long term exposure - systemic effects		1 mg/kg bw/day	
Methylsilanetriyl triacetate 4253-34-3	General population	oral	Acute/short term exposure - systemic effects		1 mg/kg bw/day	

**Biological Exposure Indices:**

None

**8.2. Exposure controls:**

## Respiratory protection:

Use only in well-ventilated areas.

Ensure adequate ventilation.

An approved mask or respirator fitted with an organic vapour cartridge should be worn if the product is used in a poorly ventilated area

Filter type: A

## Hand protection:

Chemical-resistant protective gloves (EN 374).

Suitable materials for short-term contact or splashes (recommended: at least protection index 2, corresponding to &gt; 30 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq$  0.4 mm thickness)

Suitable materials for longer, direct contact (recommended: protection index 6, corresponding to &gt; 480 minutes permeation time as per EN 374):

nitrile rubber (NBR;  $\geq$  0.4 mm thickness)

This information is based on literature references and on information provided by glove manufacturers, or is derived by analogy with similar substances. Please note that in practice the working life of chemical-resistant protective gloves may be considerably shorter than the permeation time determined in accordance with EN 374 as a result of the many influencing factors (e.g. temperature). If signs of wear and tear are noticed then the gloves should be replaced.

## Eye protection:

Wear protective glasses.

Protective eye equipment should conform to EN166.

**Skin protection:**

Wear suitable protective clothing.

Protective clothing should conform to EN 14605 for liquid splashes or to EN 13982 for dusts.

**Advices to personal protection equipment:**

The information provided on personal protective equipment is for guidance purposes only. A full risk assessment should be conducted prior to using this product to determine the appropriate personal protective equipment to suit local conditions. Personal protective equipment should conform to the relevant EN standard.

**SECTION 9: Physical and chemical properties****9.1. Information on basic physical and chemical properties**

Appearance	paste black
Odor	Acetic acid
Odour threshold	No data available / Not applicable
pH	Not applicable
Initial boiling point	Not determined
Flash point	> 150 °C (> 302 °F)
Decomposition temperature	No data available / Not applicable
Vapour pressure	< 0,1 mm hg
Density ( $\rho$ )	1,04 g/cm <sup>3</sup>
Bulk density	No data available / Not applicable
Viscosity	No data available / Not applicable
Viscosity (kinematic)	No data available / Not applicable
Explosive properties	No data available / Not applicable
Solubility (qualitative) (Solvent: Water)	Partially soluble
Solubility (qualitative) (Solvent: Acetone)	Insoluble
Solubility (qualitative)	Polymerises in presence of water.
Solidification temperature	No data available / Not applicable
Melting point	No data available / Not applicable
Flammability	No data available / Not applicable
Auto-ignition temperature	No data available / Not applicable
Explosive limits	No data available / Not applicable
Partition coefficient: n-octanol/water	No data available / Not applicable
Evaporation rate	No data available / Not applicable
Vapor density	No data available / Not applicable
Oxidising properties	No data available / Not applicable

**9.2. Other information**

No data available / Not applicable

**SECTION 10: Stability and reactivity****10.1. Reactivity**

Strong oxidizing agents.

Polymerises in presence of water.

**10.2. Chemical stability**

Stable under recommended storage conditions.

**10.3. Possibility of hazardous reactions**

See section reactivity

**10.4. Conditions to avoid**

Stable under normal conditions of storage and use.

**10.5. Incompatible materials**

See section reactivity.

**10.6. Hazardous decomposition products**

Acetic acid is liberated slowly upon contact with moisture.

At higher temperatures (>150C) may release formaldehyde (traces).

**SECTION 11: Toxicological information****11.1. Information on toxicological effects****General toxicological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

**Oral toxicity:**

May cause irritation to the digestive tract.

**Inhalative toxicity:**

Acetic acid is liberated slowly upon contact with moisture.

Inhalation of vapors in high concentration may cause irritation of respiratory system

**Skin irritation:**

Causes skin irritation.

**Eye irritation:**

Causes serious eye irritation.

Acetic acid released during polymerisation of acetoxy curing RTV silicones is irritating to the eyes

**Acute oral toxicity:**

Hazardous components CAS-No.	Value type	Value	Route of application	Exposure time	Species	Method
Methyltriacetoxysilane 4253-34-3	LD50	1.600 mg/kg	oral		rat	OECD Guideline 401 (Acute Oral Toxicity)

**SECTION 12: Ecological information****General ecological information:**

The mixture is classified based on the available hazard information for the ingredients as defined in the classification criteria for mixtures for each hazard class or differentiation in Annex I to Regulation (EC) No 1272/2008. Relevant available health/ecological information for the substances listed under Section 3 is provided in the following.

Cured Loctite products are typical polymers and do not pose any immediate environmental hazards.

In the cured state contribution of this product to Environmental Hazards is insignificant in comparison to articles in which it is used.

Precautions required with respect to Environmental Hazards of articles in which this product is used should be considered.

**12.1. Toxicity****Ecotoxicity:**

Do not empty into drains / surface water / ground water.

**12.2. Persistence and degradability****Persistence and Biodegradability:**

The product is not biodegradable.

**12.3. Bioaccumulative potential / 12.4. Mobility in soil****Mobility:**

Cured adhesives are immobile.

**Bioaccumulative potential:**

No data available for the product.

**12.5. Results of PBT and vPvB assessment**

Hazardous components CAS-No.	PBT/vPvB
Methyltriacetoxysilane 4253-34-3	Not fulfilling Persistent, Bioaccumulative and Toxic (PBT), very Persistent and very Bioaccumulative (vPvB) criteria.

**12.6. Other adverse effects**

No data available.

**SECTION 13: Disposal considerations****13.1. Waste treatment methods****Product disposal:**

Dispose of in accordance with local and national regulations.

Collection and delivery to recycling enterprise or other registered elimination institution.

**Disposal of uncleaned packages:**

After use, tubes, cartons and bottles containing residual product should be disposed of as chemically contaminated waste in an authorised legal land fill site or incinerated.

Disposal must be made according to official regulations.

**Waste code**

08 04 09 waste adhesives and sealants containing organic solvents and other dangerous substances

The valid EWC waste code numbers are source-related. The manufacturer is therefore unable to specify EWC waste codes for the articles or products used in the various sectors. The EWC codes listed are intended as a recommendation for users. We will be happy to advise you.



**SECTION 14: Transport information****14.1. UN number**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

**14.2. UN proper shipping name**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

**14.3. Transport hazard class(es)**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

**14.4. Packing group**

ADR	Not dangerous goods
RID	Not dangerous goods
ADN	Not dangerous goods
IMDG	Not dangerous goods
IATA	Not dangerous goods

**14.5. Environmental hazards**

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

**14.6. Special precautions for user**

ADR	not applicable
RID	not applicable
ADN	not applicable
IMDG	not applicable
IATA	not applicable

**14.7. Transport in bulk according to Annex II of Marpol and the IBC Code**

not applicable

**SECTION 15: Regulatory information****15.1. Safety, health and environmental regulations/legislation specific for the substance or mixture**VOC content < 5,00 %  
(2010/75/EC)**15.2. Chemical safety assessment**

A chemical safety assessment has not been carried out.

### SECTION 16: Other information

The labelling of the product is indicated in Section 2. The full text of all abbreviations indicated by codes in this safety data sheet are as follows:

H302 Harmful if swallowed.

H314 Causes severe skin burns and eye damage.

**Further information:**

This information is based on our current level of knowledge and relates to the product in the state in which it is delivered. It is intended to describe our products from the point of view of safety requirements and is not intended to guarantee any particular properties.

**Relevant changes in this safety data sheet are indicated by vertical lines at the left margin in the body of this document. Corresponding text is displayed in a different color on shadowed fields.**