

**KEMET Part Number: C1812C474G3JACTU**  
(C1812C474G3JAC7800)

SMD Comm U2J, Ceramic, 0.47 uF, 2%, 25 V, U2J, SMD, MLCC, Ultra-Stable, Low Loss, Class I, 1812



**Dimensions**

<b>L</b>	4.5mm +/-0.3mm
<b>W</b>	3.2mm +/-0.3mm
<b>T</b>	1.6mm +/-0.20mm
<b>B</b>	0.6mm +/-0.35mm

**Packaging Specifications**

<b>Packaging:</b>	T&R, 180mm, Plastic Tape
<b>Packaging Quantity:</b>	1000

**General Information**

<b>Supplier:</b>	KEMET
<b>Series:</b>	SMD Comm U2J
<b>Style:</b>	SMD Chip
<b>Description:</b>	SMD, MLCC, Ultra-Stable, Low Loss, Class I
<b>Features:</b>	Ultra-Stable, Low Loss, Class I
<b>RoHS:</b>	Yes
<b>Termination:</b>	Tin
<b>Marking:</b>	No
<b>Failure Rate:</b>	N/A
<b>Miscellaneous:</b>	Note: Referee time for U2J dielectric for this part number is 1000 hours
<b>Chip Size:</b>	1812

**Specifications**

<b>Capacitance:</b>	0.47 uF
<b>Capacitance Tolerance:</b>	2%
<b>Voltage DC:</b>	25 VDC
<b>Dielectric Withstanding Voltage:</b>	62.5 V
<b>Temperature Range:</b>	-55/+125C
<b>Temperature Coefficient:</b>	U2J
<b>Dissipation Factor:</b>	0.1% 1kHz 25C
<b>Aging Rate:</b>	0.1% Loss/Decade Hour
<b>Insulation Resistance:</b>	2.128 GOhms