

TECHNICAL DATA SHEET



Multi Core Stage Cable Model: CB13323

RoHS
Compliant

Design of cable:	
Inner conductor	20/0.10 bare copper OFC
Insulation	PE
Colour	Red, white
Diameter/thickness	1.1 ± 0.10mm / 0.29 ± 0.08mm
Drain wire	DW7/0.20TC
Wrap	AL foil
Covering	PVC
Diameter/thickness	3.0 ± 0.10mm / 1.3 ± 0.15mm
Jacket	PVC
Colour	Blue
Size	10.0 ± 0.03mm dia ± 0.15mm
Wall thickness	0.65 ± 0.1mm
Printing	Multi Pair Stage Cable
Electric data at 20°C	
Conductor resistance	83.3Ω
Capacitance	65.6pF/m
Voltage	30V DC
Packing	100m on wooden reels
Temperature range	-10°C ~ 60°C

Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

