

TECHNICAL DATA SHEET





Weather Resistant Cable Ties

**RoHS
Compliant**

Materials Used:	
Main component	Nylon 66, 94V-2 certificated by UL
Operating temperature	-35°C to 85°C
Main Features	
Heat, acid and erosion resistant. Good insulation Releasable	

ITEM No	Length (mm)	Width (mm)	Max Bundle Dia (mm)	Tensile Strength		Colour
				Lbs	Kgs	
CBBR7702	100	2.5	2-22	18	8	UV Black
CBBR7703	120	4.5	3-24	50	22	
CBBR7704	140	2.5	2-33	18	8	
CBBR7705	150	3.2	3-35	40	18	
CBBR7706	160	2.5	2-40	18	8	
CBBR7707	160	4.5	3-42	50	22	
CBBR7708	200	2.5	3-50	18	8	
CBBR7709	200	3.5	3-50	40	18	
CBBR7710	200	4.5	3-50	50	22	
CBBR7711	300	3.5	3-80	40	18	
CBBR7712	300	4.5	3-82	50	22	
CBBR7713	370	3.5	3-102	40	18	
CBBR7714	380	4.8	3-102	50	22	
CBBR7715	370	7.5	4-98	120	55	



Important Notice : This data sheet and its contents (the "Information") belong to pro-POWER. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but pro-POWER assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where pro-POWER was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict pro-POWER's liability for death or personal injury resulting from its negligence.

