














Amp	Volt	Hz	IP Ident. colour +h	Part No.	Wall mount appliance inlets	3 P + N + \perp IEC/EN 60 309	 	EAN No. 4015609...																																
					external fixing means, 1 top cable entry																																			
																																								
16	400	50/60	6	610			10/60	000890 023240 023264 023288																																
	110	50/60	4	610 504																																				
	230	50/60	9	610 509																																				
	440	60	11	610 511																																				
32	400	50/60	6	630			10	000951 024155 024179 024186																																
	110	50/60	4	630 504																																				
	230	50/60	9	630 509																																				
	440	60	11	630 511																																				
						<table border="1"> <thead> <tr> <th>Ampère</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>l</th> <th>n</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>60</td> <td>5,3</td> <td>80</td> <td>74</td> <td>73</td> <td>31</td> <td>117</td> <td>16</td> </tr> <tr> <td>32 A</td> <td>60</td> <td>5,3</td> <td>97</td> <td>82</td> <td>86</td> <td>45</td> <td>141</td> <td>21</td> </tr> </tbody> </table>	Ampère	b	c	d	e	f	l	n	Pg	16 A	60	5,3	80	74	73	31	117	16	32 A	60	5,3	97	82	86	45	141	21							
Ampère	b	c	d	e	f	l	n	Pg																																
16 A	60	5,3	80	74	73	31	117	16																																
32 A	60	5,3	97	82	86	45	141	21																																
					internal fixing means, 2 cable entries both, top and bottom (knock-out)																																			
																																								
16	400	50/60	6	616			5	000920 157884 146154 157877																																
	110	50/60	4	616 504																																				
	230	50/60	9	616 509																																				
	440	60	11	616 511																																				
32	400	50/60	6	636			5	000982 166992 128556 167005																																
	110	50/60	4	636 504																																				
	230	50/60	9	636 509																																				
	440	60	11	636 511																																				
						<table border="1"> <thead> <tr> <th>Ampère</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>l</th> <th>n</th> <th>v</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>66,5</td> <td>5</td> <td>96</td> <td>95</td> <td>140</td> <td>47,5</td> <td>151</td> <td>7</td> <td>16/21</td> </tr> <tr> <td>32 A</td> <td>66,5</td> <td>5</td> <td>96</td> <td>95</td> <td>140</td> <td>47,5</td> <td>160</td> <td>7</td> <td>16/21</td> </tr> </tbody> </table>	Ampère	b	c	d	e	f	l	n	v	Pg	16 A	66,5	5	96	95	140	47,5	151	7	16/21	32 A	66,5	5	96	95	140	47,5	160	7	16/21				
Ampère	b	c	d	e	f	l	n	v	Pg																															
16 A	66,5	5	96	95	140	47,5	151	7	16/21																															
32 A	66,5	5	96	95	140	47,5	160	7	16/21																															
					internal fixing means, 2 cable entries both, top and bottom (knock-out)																																			
																																								
16	400	50/60	6	618			5	000937 165803 023899 165810																																
	110	50/60	4	618 504																																				
	230	50/60	9	618 509																																				
	440	60	11	618 511																																				
					cable gland Pg 16 enclosed																																			
32	400	50/60	6	638			5	000999 167050 024711 024728																																
	110	50/60	4	638 504																																				
	230	50/60	9	638 509																																				
	440	60	11	638 511																																				
					cable gland Pg 21 enclosed																																			
						<table border="1"> <thead> <tr> <th>Ampère</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>l</th> <th>n</th> <th>u</th> <th>v</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>16 A</td> <td>66,5</td> <td>5</td> <td>96</td> <td>95</td> <td>140</td> <td>47,5</td> <td>154</td> <td>88</td> <td>7</td> <td>16/21</td> </tr> <tr> <td>32 A</td> <td>66,5</td> <td>5</td> <td>96</td> <td>95</td> <td>150</td> <td>47,5</td> <td>164</td> <td>103</td> <td>7</td> <td>16/21</td> </tr> </tbody> </table>	Ampère	b	c	d	e	f	l	n	u	v	Pg	16 A	66,5	5	96	95	140	47,5	154	88	7	16/21	32 A	66,5	5	96	95	150	47,5	164	103	7	16/21	
Ampère	b	c	d	e	f	l	n	u	v	Pg																														
16 A	66,5	5	96	95	140	47,5	154	88	7	16/21																														
32 A	66,5	5	96	95	150	47,5	164	103	7	16/21																														
					external fixing means, 1 top cable entry																																			
63	400	50/60	6	668			2	001033 024971 024995 025008																																
	110	50/60	4	668 504																																				
	230	50/60	9	668 509																																				
	440	60	11	668 511																																				
125	see page 2/41						891																																	
						<table border="1"> <thead> <tr> <th>Ampère</th> <th>a</th> <th>b</th> <th>c</th> <th>d</th> <th>e</th> <th>f</th> <th>n</th> <th>u</th> <th>Pg</th> </tr> </thead> <tbody> <tr> <td>63 A</td> <td>120</td> <td>106</td> <td>5,6</td> <td>152</td> <td>118</td> <td>118</td> <td>232</td> <td>113</td> <td>29</td> </tr> </tbody> </table>		Ampère	a	b	c	d	e	f	n	u	Pg	63 A	120	106	5,6	152	118	118	232	113	29													
Ampère	a	b	c	d	e	f	n	u	Pg																															
63 A	120	106	5,6	152	118	118	232	113	29																															