

LED PIPE 1500

LED PIPE 1500 2000LM 22W L1200 3000K

0051018

Product features

- LED Batten T5 1500lm per metre, 2000LM, 22W, L1200, 3000K, 120 degree beam angle, includes switch, includes stripped cable (75cm), white polycarbonate body, dimensions length 1182mm, width 24mm, height 36mm, includes standard and tilting brackets, linkable up to 10m.

PRODUCT OVERVIEW

Certifications	CE
Colour temperature (K)	3000
Colour	White
CRI (Ra)	80
EAN code	5410288510187
Luminous flux (lm)	2000
Housing	Polycarbonate
IP rating	IP20
Light colour	Warm white
LOR (%)	100
Mount	Surface mounted
Ordering number	0051018
Efficacy (Rated) (lm/w)	91
Average life (h) - L70/B50	30000
Technology	LED
Voltage (V)	100-240
Included lamp	Integrated LED

DATA TABLE

General data

Certifications	CE
EAN code	5410288510187
Environment	Internal
General application	Residential & Consumer
Housing	Polycarbonate
Mount	Surface mounted
Ordering number	0051018
Product name	LED PIPE 1500 2000LM 22W L1200 3000K
Average life (h) - L70/B50	30000
Technology	LED

LED PIPE 1500

LED PIPE 1500 2000LM 22W L1200 3000K

0051018

Product features	LED Batten T5 1500lm per metre, 2000LM, 22W, L1200, 3000K, 120 degree beam angle, includes switch, includes stripped cable (75cm), white polycarbonate body, dimensions length 1182mm, width 24mm, height 36mm, includes standard and tilting brackets, linkable up to 10m.
-------------------------	---

What temperature Life is measured at (°C): 25

Optical data

Colour temperature (K)	3000
CRI (Ra)	80
Distribution type	Direct
Luminous flux (lm)	2000
Light colour	Warm white
LOR (%)	100

Physical data

Colour	White
Diffuser finish	Frosted
Height (mm)	36
IP rating	IP20
Lamp included	Integrated
Length (mm)	1182
Width (mm)	24
Included lamp	Integrated LED

Electrical data


Electrical protection	CLASS 2
Efficacy (Rated) (lm/w)	91
Total power consumption (W)	22
Voltage (V)	100-240

PHOTOMETRY

LED PIPE 1500

LED PIPE 1500 2000LM 22W L1200 3000K


0051018



Distance [m]	Cone diameter [m]	E [lx]	E (C90) [lx]	E (C0) [lx]
0.5	10.78 1.43	1739 1	84.7° 183	55.1° 183
1.0	21.56 2.87	435 0	84.7° 41	55.1° 41
1.5	32.34 4.30	190 0	84.7° 18	55.1° 18
2.0	43.12 5.73	109 0	84.7° 10	55.1° 10
2.5	53.90 7.17	70 0	84.7° 7	55.1° 7
3.0	64.68 8.60	48 0	84.7° 5	55.1° 5

Distance [m] Cone diameter [m] Illuminance [lx]
 — C0 - C180 (Half beam angle: 110.2°)
 — C90 - C270 (Half beam angle: 169.4°)

TECHNICAL DRAWINGS




Power	L1	L2	W	H
4/6W	270mm	262mm	24mm	36mm
7/11W	570mm	562mm	24mm	36mm
10/17W	670mm	862mm	24mm	36mm
14/22W	1170mm	1162mm	24mm	36mm


LED PIPE 1500

LED PIPE 1500 2000LM 22W L1200 3000K


0051018


SYLVANIA 0051018


 This luminaire contains built in LED lamps.


} **LED**


The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built in LED lamps.


} **LED**

The lamps cannot be changed in the luminaire.

SYLVANIA 0051018 

874/2012