

LED PIPE 1500

LED PIPE 1500 520LM 6W L300 4000K

0051019



Product features

- LED Batten T5 1500lm per metre, 520LM, 6W, L300, 4000K, 120 degree beam angle, includes switch, includes stripped cable (75cm), white polycarbonate body, dimensions length 282mm, width 24mm, height 36mm, includes standard and tilting brackets, linkable up to 10m.

PRODUCT OVERVIEW

Certifications	CE
Colour temperature (K)	4000
Colour	White
CRI (Ra)	80
EAN code	5410288510194
Luminous flux (lm)	520
Housing	Polycarbonate
IP rating	IP20
Light colour	Cool white
LOR (%)	100
Mount	Surface mounted
Ordering number	0051019
Efficacy (Rated) (lm/w)	87
Average life (h) - L70/B50	30000
Technology	LED
Voltage (V)	100-240
Included lamp	Integrated LED

DATA TABLE

General data

Certifications	CE
EAN code	5410288510194
Environment	Internal
General application	Residential & Consumer
Housing	Polycarbonate
Mount	Surface mounted
Ordering number	0051019
Product name	LED PIPE 1500 520LM 6W L300 4000K
Average life (h) - L70/B50	30000
Technology	LED

LED PIPE 1500

LED PIPE 1500 520LM 6W L300 4000K

0051019

Product features	LED Batten T5 1500lm per metre, 520LM, 6W, L300, 4000K, 120 degree beam angle, includes switch, includes stripped cable (75cm), white polycarbonate body, dimensions length 282mm, width 24mm, height 36mm, includes standard and tilting brackets, linkable up to 10m.
-------------------------	---

What temperature Life is measured at (°C): 25

Optical data

Colour temperature (K)	4000
CRI (Ra)	80
Distribution type	Direct
Luminous flux (lm)	520
Light colour	Cool white
LOR (%)	100

Physical data

Colour	White
Diffuser finish	Frosted
Height (mm)	36
IP rating	IP20
Lamp included	Integrated
Length (mm)	282
Width (mm)	24
Included lamp	Integrated LED

Electrical data

Electrical protection	CLASS 2
Efficacy (Rated) (lm/w)	87
Total power consumption (W)	6
Voltage (V)	100-240

PHOTOMETRY

LED PIPE 1500


LED PIPE 1500 520LM 6W L300 4000K

0051019


Distance [m]	Cone diameter [m]	E(0°) E(C90) E(C0)	45° 0 0
0.5	21.20 1.38	87.3° 54.1°	491 46
1.0	42.41 2.76	87.3° 54.1°	113 9 11
1.5	63.61 4.14	87.3° 54.1°	50 0 6
2.0	84.82 5.53	87.3° 54.1°	28 0 3
2.5	106.02 6.91	87.3° 54.1°	18 0 2
3.0	127.23 8.29	87.3° 54.1°	13 0 1

Distance [m] Cone diameter [m] Illuminance [lx]

— C0 - C180 (Half beam angle: 108.2°)
— C90 - C270 (Half beam angle: 174.6°)



TECHNICAL DRAWINGS




Power	L1	L2	W	H
4/6W	270mm	282mm	24mm	36mm
7/11W	570mm	582mm	24mm	36mm
10/17W	670mm	682mm	24mm	36mm
14/22W	1170mm	1182mm	24mm	36mm


LED PIPE 1500

LED PIPE 1500 520LM 6W L300 4000K


0051019


SYLVANIA 0051019

 This luminaire contains built in LED lamps.


 } **LED**


The lamps cannot be changed in the luminaire.

874/2012 

 This luminaire contains built in LED lamps.

The lamps cannot be changed in the luminaire.

 } **LED**

SYLVANIA 0051019  874/2012