

LADT4

TeSys D - time delay auxiliary contact block - 1 NO + 1 NC screw clamp terminals

Product availability : Stock - Normally stocked in distribution facility



Main

Range of product	TeSys D TeSys F
Range	TeSys
Product or component type	Time delay auxiliary contact block
Pole contact composition	1 NO + 1 NC
Shielding continuity terminal	Without
Connections - terminals	Screw clamp terminals 1 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: flexible - with cable end Screw clamp terminals 1 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: flexible - without cable end Screw clamp terminals 1 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: solid - with cable end Screw clamp terminals 1 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: solid - without cable end Screw clamp terminals 2 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: flexible - with cable end Screw clamp terminals 2 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: flexible - without cable end Screw clamp terminals 2 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: solid - with cable end Screw clamp terminals 2 cable 0...0 in ² (1...2.5 mm ²) - cable stiffness: solid - without cable end

Complementary

Mounting location	Front
[Ui] rated insulation voltage	690 V - conforming to IEC 60947-5-1 600 V - certifications CSA 600 V - certifications UL
System Voltage	690 V AC 25...400 Hz
[I _{th}] conventional free air thermal current	10 A at ≤ 140 °F (60 °C)
I _{rms} rated making capacity	140 A at ≤ 690 V AC conforming to IEC 60947-5-1 250 A at ≤ 690 V DC conforming to IEC 60947-5-1
Permissible short-time rating	100 A at 60 °C 1 s 120 A at 60 °C 500 ms 140 A at 60 °C 100 ms
Protection type	GG fuse ≤ 10 A rating according to operational current for U _e ≤ 690 V
Associated fuse rating	10 A gG IEC 60947-5-1
Mechanical durability	5 Mcycles
Minimum switching current	5 mA
Minimum switching voltage	17 V
Non-overlap time	1.5 ms on de-energisation (no overlap between NC and NO contact)

1.5 ms on energisation (no overlap between NC and NO contact)

Timer type	On delay
Time delay range	10...180 s
Insulation resistance	> 10 MOhm

Environment

Environmental characteristic	Normal environment
Standards	EN 60947-5-1 NF C 63-140 VDE 0660 IEC 60947-5-1 BS 4794
Product certifications	UL CSA
IP degree of protection	IP2x conforming to VDE 0106
Protective treatment	TH conforming to IEC 60068
Ambient air temperature for operation	23...140 °F (-5...60 °C)
Ambient air temperature for storage	-76...176 °F (-60...80 °C)
Operating altitude	9842.52 ft (3000 m) without derating in temperature

Ordering and shipping details

Category	22341 - CONTACTOR,D,K,&F ACCESS
Discount Schedule	I12
GTIN	00785901213833
Nbr. of units in pkg.	1
Package weight(Lbs)	0.17000000000000001
Returnability	Y
Country of origin	FR

Contractual warranty

Warranty period	18 months
-----------------	-----------