

# Antenna tripod for Tektronix EMC pre-compliance

EMI-TRIPOD (Com-Power AT-812 offered by Tektronix)



The Tektronix EMI-TRIPOD is the Com-Power AT-812 antenna tripod that supports the ABF-900 and ALC-100 antennas for EMC testing. The tripod is made of non reflective nylon and wood material. The antenna height can be easily adjusted by moving the center slotted rod up or down. The tripod is designed to be portable so that the antenna can be placed at the appropriate location for testing. The tripod legs can be folded for easy transport and storage.

## Key features

- Made of nylon material
- For EMC antennas
- Mounts a variety of antennas
- Portable

## Specifications

### Antenna tripod

**Antenna height range** 0.8 – 1.2 meters

**Construction** Wood and nylon

**For Com-Power antenna models** AL-100, ALP-100, ALC-100 (Tektronix EMI-CLP-ANT), AC-220, AH-8055, AL-130, AH-118, AHA-118, AH-640, AH-826, AH-840, AHA-840, AB-900A, ABF-900 (Tektronix EMI-BICON-ANT), ABM-6000, AD-1000

---

## Ordering information

### EMI-TRIPOD antenna tripod and related accessories

Item	Description
EMI-TRIPOD	Antenna Tripod, Wood-Nylon, 0.8 to 1.5 meter adjustable height
EMI-BICON-ANT	25 MHz to 300 MHz collapsible biconical antenna
EMI-CLP-ANT	100 MHz to 1 GHz compact log periodic antenna

### Warranty

Three year warranty. All service provided by Com-Power Corporation. Contact <https://www.com-power.com/index.html> for service.

**ASEAN / Australasia** (65) 6356 3900  
**Belgium** 00800 2255 4835\*  
**Central East Europe and the Baltics** +41 52 675 3777  
**Finland** +41 52 675 3777  
**Hong Kong** 400 820 5835  
**Japan** 81 (3) 6714 3086  
**Middle East, Asia, and North Africa** +41 52 675 3777  
**People's Republic of China** 400 820 5835  
**Republic of Korea** +822 6917 5084, 822 6917 5080  
**Spain** 00800 2255 4835\*  
**Taiwan** 886 (2) 2656 6688

**Austria** 00800 2255 4835\*  
**Brazil** +55 (11) 3759 7627  
**Central Europe & Greece** +41 52 675 3777  
**France** 00800 2255 4835\*  
**India** 000 800 650 1835  
**Luxembourg** +41 52 675 3777  
**The Netherlands** 00800 2255 4835\*  
**Poland** +41 52 675 3777  
**Russia & CIS** +7 (495) 6647564  
**Sweden** 00800 2255 4835\*  
**United Kingdom & Ireland** 00800 2255 4835\*

**Balkans, Israel, South Africa and other ISE Countries** +41 52 675 3777  
**Canada** 1 800 833 9200  
**Denmark** +45 80 88 1401  
**Germany** 00800 2255 4835\*  
**Italy** 00800 2255 4835\*  
**Mexico, Central/South America & Caribbean** 52 (55) 56 04 50 90  
**Norway** 800 16098  
**Portugal** 80 08 12370  
**South Africa** +41 52 675 3777  
**Switzerland** 00800 2255 4835\*  
**USA** 1 800 833 9200

\* European toll-free number. If not accessible, call: +41 52 675 3777

**For Further Information.** Tektronix maintains a comprehensive, constantly expanding collection of application notes, technical briefs and other resources to help engineers working on the cutting edge of technology. Please visit [www.tek.com](http://www.tek.com).

Copyright © Tektronix, Inc. All rights reserved. Tektronix products are covered by U.S. and foreign patents, issued and pending. Information in this publication supersedes that in all previously published material. Specification and price change privileges reserved. TEKTRONIX and TEK are registered trademarks of Tektronix, Inc. All other trade names referenced are the service marks, trademarks, or registered trademarks of their respective companies.



08 Feb 2018 37W-61337-0

