


HD-TVI 2MP IR Bullet Camera

VLB2TW 3.6mm fixed lens, white housing

Features

- Full HD resolution over coax (HD-TVI)
- Supports up to Full HD 1080p @ 30fps
- Full OSD operation through on-board control and UTC (up the coax)
- 28 built-in IR LEDs
- 3 axis lens mount
- Adapter plate in optional accessories included
- Additional analog output for 960H
- Signal distance up to 1600 ft.¹
- 12VDC operation (power supply not included)
- IP66 compliant, weather resistant
- 5 year warranty²



Specifications

Image Sensor	1/3" 2MP CMOS
Resolution.....	1080p/720p
Minimum Illumination.....	0 lux @F2.0 (IR on) / 0.1 lux @F2.0 (IR off)
S/N Ratio	50dB
Motion Detection.....	Yes
Day/Night.....	IR-cut filter
DNR.....	2D/3D Automatic
Number of IR LEDs	28
IR Range	60' (depending on scene reflection)
Power Supply	12VDC (power supply not included)
Power Consumption	400mA (IR on)
Operating Temperature.....	-4° F - 104° F
Weight	9.6 oz.
Dimensions.....	2.5" (Dia.) x 7.2" (L)

Optional Accessories



INTJBSW
Square
Junction Box



INTCMW
Corner/Pole
Adapter



CVCJBBW
Bullet Camera
Junction Box



PSW5
12VDC
Power Supply



TVIUTPPT
HD Video
Transceiver with
Pigtail (Balun)



TVIUPT
HD Video
Transceiver

¹To preserve signal quality and distance, Speco Technologies recommends using coax with a 100% copper center conductor and at least 95% braided copper shield.

²Effective on all new purchases as of 2/1/17. Speco Technologies is constantly developing and improving products. We reserve the right to modify product design and specifications without notice and without incurring any obligation. Spec Rev. 7/6/17