

Product data sheet

Characteristics

P1T

APC single outlet travel surge protector with phone line protection, 120V



Overview

Model Name	APC single outlet travel surge protector with phone line-protection, 120V
Includes	RJ11 Cable , User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And-Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

Output

Number of Outlets	1
Receptacle Style	NEMA 5-15R

Input

Nominal Input Voltage	120V
Input Power	0 W
Input Frequency	50/60 Hz +/- 5 Hz (auto sensing)
Input Connections	NEMA 5-15P
Maximum Line Current per phase	15.0 A
Maximum Input Current	0 A

Surge Protection and Filtering

Surge energy rating	540 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Normal Mode	4.5 kA
Peak Current Common Mode	9.0 kA
NM Surge Response Time (ns)	0.0 NS
Data Line Protection	RJ-11 Modem/Fax protection (two wire single line)
Data Lines Protected (multi-line only)	1
Let Through Voltage Rating	330

Physical

Net Weight	0.18 lbs (0.08 kg)
Maximum Height	3.0 inches (76.0 mm)
Maximum Width	2.12 inches (54.0 mm)
Maximum Depth	2.26 inches (57.0 mm)
Shipping Weight	0.32 lbs (0.16 kg)
Shipping Height	4.6 inches (117.0 mm)
Shipping Width	6.1 inches (155.0 mm)
Shipping Depth	2.6 inches (66.0 mm)

Master Carton Units	12.0
Master Carton Weight	4.85 lbs
SCC Codes	1073130421835 4
Color	Charcoal
Units per Pallet	0.0

Environmental

Operating Environment	32 - 104 °F (0 - 40 °C)
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-10000 feet (0-3000 meters)
Storage Temperature	5 - 113 °F (-15 - 45 °C)
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-50000 feet (0-15000 meters)

Conformance

Approvals	UL 1449 , UL 489
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$25000
UL 1449 TVSS Rating	330

Sustainable Offer Status

RoHS	Compliant
------	-----------