

# P6GC

## APC Power-Saving Timer Essential SurgeArrest, 6 Outlet, 120V



### Overview

Model Name	APC Power-Saving Timer Essential SurgeArrest, 6 Outlet, 120V
Includes	User Manual
Standard Lead Time	Usually in Stock
Product Distribution	Anguilla , Aruba , Bahamas , Barbados , Belize , Bermuda , Canada , Colombia , Costa Rica , Cuba , Dominican Republic , Ecuador , El Salvador , Guatemala , Guyana , Haiti , Honduras , Jamaica , Mexico , Netherlands Antilles , Nicaragua , Panama , Puerto Rico , Trinidad And Tobago , Turks And Caicos Islands , United States , Venezuela , VIRGIN ISLANDS (UNITED STATES)

### Output

Number of Outlets	6
Receptacle Style	NEMA 5-15R

### Input

Nominal Input Voltage	120V
Input Power	0 W
Input Frequency	50/60 Hz
Input Connections	NEMA 5-15P
Maximum Line Current per phase	0.0 A
Cord Length	0.91 meters
Maximum Input Current	15 A

### Surge Protection and Filtering

Surge energy rating	1080 Joules
EMI/RFI Noise rejection (100 kHz to 10 MHz)	40.0 dB
Peak Current Common Mode	72.0 kA
NM Surge Response Time (ns)	1.0 NS

### Physical

Net Weight	0.59 kg
Maximum Height	362.0 mm
Maximum Width	57.0 mm
Maximum Depth	46.0 mm
Shipping Weight	0.72 kg
Shipping Height	476.0 mm
Shipping Width	171.0 mm
Shipping Depth	51.0 mm
Master Carton Units	6.0
Master Carton Dimensions (Length x Width x Height)	15.8 x 10 x 20.8 inches
Master Carton Weight	5.8 kg
SCC Codes	1073130426925 7
Color	White
Units per Pallet	216.0

The information provided in this documentation contains general descriptions and/or technical characteristics of the performance of the products contained herein. This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications. It is the duty of any such user or integrator to perform the appropriate and complete risk analysis, evaluation and testing of the products with respect to the relevant specific application or use thereof. Neither Schneider Electric Industries SAS nor any of its affiliates or subsidiaries shall be responsible or liable for misuse of the information contained herein.

## Environmental

Operating Environment	0 - 45 °C
Operating Relative Humidity	0 - 95 %
Operating Elevation	0-3000 meters
Storage Temperature	-5 - 45 °C
Storage Relative Humidity	0 - 95 %
Storage Elevation	0-15000 meters

## Conformance

Approvals	ETL , UL 1449
Standard warranty	Lifetime
Equipment protection policy	Lifetime : \$50000
UL 1449 TVSS Rating	<![CDATA[<400]]>

## Sustainable Offer Status

RoHS	Compliant
REACH	REACH: Contains No SVHCs