



Main

Range	TeSys
Product name	TeSys LE
Device short name	LE1M
Product or component type	Enclosed DOL starter
Device application	Standard
Utilisation category	AC-3
Device composition	Neutral terminal Earth terminal Thermal overload relay Contactor
Thermal protection adjustment range	1.8...2.6 A
Motor power kW	1.1 kW at 380/400 V AC 50/60 Hz 0.37 kW at 220/230 V AC 50/60 Hz 0.37 kW at 240 V AC 50/60 Hz 0.75 kW at 415 V AC 50/60 Hz
[Uc] control circuit voltage	240 V AC 50/60 Hz
Control type	Push-button start green I Push-button stop/reset red O

Complementary

Local signalling	LED yellow operating
Cable entry number	2 cable entry : Pg 13 top 2 cable entry : ISO20 top 2 cable entry : ISO20 bottom 2 cable entry : Pg 13 bottom 2 cable entry : Pg 16 bottom 2 cable entry : ISO25 top 2 cable entry : Pg 21 bottom 2 cable entry : ISO25 bottom 2 cable entry : Pg 21 top 2 cable entry : Pg 16 top
Width	78 mm
Height	160 mm
Depth	108 mm
Product weight	0.6 kg

Environment

Material	ABS (acrylonitrile butadiene-styrene)
IP degree of protection	IP65 conforming to IEC 60529
Standards	IEC 60947-4-1
Ambient air temperature for operation	-5...40 °C
Environmental characteristic	Standard environment

Contractual warranty

Warranty period	18 months
-----------------	-----------