



Part Number: 1306SB

Composite Shipboard, 18 AWG Coax Video, 1 PR 18 AWG Power

Product Description

Composite Shipboard, 18 AWG Coax BC, BC Braid Shield 95% coverage, FPE insulation for video and 1 PR 18 AWG BC, stranded (7x26), PP insulation for power, overall CMG-LS rating, LSZH jacket.

Technical Specifications

Product Overview

Environmental Space:	Outdoor - Aerial
Suitable Applications:	Security Composite Communications Cable for CCTV plus Audio or PTZ (Pan/Tilt/Zoom) CCTV Control Applications in Marine Shipboard and Offshore use

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Pairs	No. of Coax
18	Solid	BC - Bare Copper	0.04 in	1	1
18	7x26	BC - Bare Copper	0.046 in		

Conductor Count:	3
------------------	---

Insulation

Material	Nominal Diameter
FPE - Foamed Polyethylene	0.18 in
PP - Polypropylene	0.058 in

Color Chart

Number	Color
1	Black and Red

Inner Shield Material

Type	Material	Coverage [%]
Braid	BC - Bare Copper	95 %

Outer Shield Material

Type	Layer	Material	Coverage [%]
Braid	1	BC - Bare Copper	95 %

Outer Jacket Material

Material	Nominal Diameter
LSZH - Low Smoke Zero Halogen	0.275x0.514 in

Electrical Characteristics

Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR	Conductor Resistance	Nominal Inner Shield DCR	Outer Conductor DCR
6.4 Ohm/1000ft	6.4 Ohm/1000ft		3.1 Ohm/1000ft	3.1 Ohm/1000ft
6.4 Ohm/1000ft				

Capacitance

Nom. Capacitance Conductor to Conductor	Nom. Capacitance Conductor to Shield
24 pF/ft	16.3 pF/ft

Operating Voltage:	300 V RMS
--------------------	-----------

Inductance

Nominal Inductance
0.097 µH/ft

Impedance

Nominal Characteristic Impedance
75 Ohm

High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss
1 MHz	0.2 dB/100ft
5 MHz	0.45 dB/100ft
10 MHz	0.64 dB/100ft
50 MHz	1.46 dB/100ft
100 MHz	2.1 dB/100ft
200 MHz	3.0 dB/100ft
400 MHz	4.3 dB/100ft
700 MHz	5.8 dB/100ft
900 MHz	6.7 dB/100ft
1000 MHz	7.1 dB/100ft

Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.24 ns/ft	82 %

Voltage

UL Voltage Rating
300 V RMS

Temperature Range

Operating Temp Range:	-30°C To +75°C
-----------------------	----------------

Mechanical Characteristics

UV Resistance:	Yes - Black only
Bulk Cable Weight:	67 lbs/1000ft
Max Recommended Pulling Tension:	114 lbs
Min Bend Radius/Minor Axis:	2.75 in

Standards

NEC Articles:	800
NEC/(UL) Specification:	CMG-LS
CEC/C(UL) Specification:	CMG-LS
CPR Euroclass:	Fca
IEEE Specification:	Std. 45 Clause 23
RG Type:	RG-6/U Type
Other Specification:	UL444, ABS Type Approval Certificate 15-VS1420030

Applicable Environmental and Other Programs

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	Yes
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-08-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Aerial:	Yes - Black only, when supported by messenger wire
Suitability - Burial:	No
Suitability - Hazardous Locations:	No
Suitability - Indoor:	Yes
Suitability - Outdoor:	Yes - Black only
Suitability - Sunlight Resistance:	No

Flammability, LSOH, Toxicity Testing

UL Flammability:	UL1685 FT4 Loading, Limited Smoke
CSA Flammability:	FT4
ISO/IEC Flammability:	60332-1, 60332-3-22 (Category A)
IEEE Flammability:	1202

Part Number

Plenum (Y/N):	No
Footnote:	C - CRATE REEL PUT-UP.

Product Notes

Notes:	Coax jacket diameter: .274 in, Pair jacket diameter: .204 in
--------	--

© 2018 Belden, Inc
All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.