

Part Number: 7927A

DataTuff® Cat 6, (4 pr) 23 AWG Solid BC, PO/PVC, CMR



Product Description

Four Cat 6 23 AWG Bonded-Pairs solid bare copper conductors, polyolefin insulation, E-Spline center member, industrial grade oil- and UV-resistant PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	Industrial Ethernet Cable, Harsh Environments, 600 MHz Enhanced Category 6, Gigabit Ethernet, 100BaseTX, 100BaseVG ANYLAN, 155ATM, 622ATM, NTSC/PAL Component or Composite Video, AES/EBU Digital Audio, AES51, RS-422, RJ-45 Compatible
------------------------	--

Physical Characteristics (Overall)

Conductor

AWG	Stranding	Material	No. of Pairs
23	Solid	BC - Bare Copper	4

Conductor Count:	8
Total Number of Pairs:	4
AWG Size:	23

Insulation

Material
PO - Polyolefin

Color Chart

Number	Color
1	White/Green & Green
2	White/Orange & Orange
3	White/Blue & Blue
4	White/Brown & Brown

Outer Shield Material

Material
Unshielded

Outer Jacket Material

Material	Nominal Diameter	Ripcord
Industrial Grade PVC - Polyvinyl Chloride	.251 x .339 in	Yes

Construction and Dimensions

Cabling

Filler
E-Spline Center Member

Electrical Characteristics

Conductor DCR

Max. Conductor DCR	Max. DCR Unbalance
8.2 Ohm/1000ft	3 %

Capacitance

Max. Capacitance Unbalance	Nom. Mutual Capacitance
65.6 pF/ft	15.5 pF/ft

Delay

Max. Delay	Max. Delay Skew	Nominal Velocity of Propagation (VP) [%]
538 ns/100m	38 ns/100m	67 %

High Freq

Frequency [MHz]	Max. Insertion Loss (Attenuation)	Min. NEXT [dB]	Min. PSNEXT [dB]	Min. ACR [dB]	Min. PSACR [dB]	Min. ACRF (ELFEXT) [dB]	Min. PSACRF (PSELFEXT) [dB]	Min. RL (Return Loss) [dB]	Min. SRL (Structural Return Loss)	Max./Min. Input Impedance (unFitted)
1 MHz	1.9 dB/100m	82.3 dB	80.3 dB	80.5 dB	78.5 dB	73.8 dB	70.8 dB	20 dB	27 dB	100 ± 12 Ohm
4 MHz	3.6 dB/100m	73.3 dB	71.3 dB	69.7 dB	67.7 dB	61.8 dB	58.8 dB	23 dB	27 dB	100 ± 12 Ohm
8 MHz	5.1 dB/100m	68.8 dB	66.8 dB	63.7 dB	61.7 dB	55.7 dB	52.7 dB	24.5 dB	27 dB	100 ± 12 Ohm
10 MHz	5.7 dB/100m	67.3 dB	65.3 dB	61.6 dB	59.6 dB	53.8 dB	50.8 dB	25 dB	27 dB	100 ± 12 Ohm
16 MHz	7.2 dB/100m	64.3 dB	62.3 dB	57 dB	55 dB	49.7 dB	46.7 dB	25 dB	27 dB	100 ± 12 Ohm
20 MHz	8.1 dB/100m	62.8 dB	60.8 dB	54.7 dB	52.7 dB	47.8 dB	44.8 dB	25 dB	27 dB	100 ± 12 Ohm
25 MHz	9.1 dB/100m	61.3 dB	59.3 dB	52.3 dB	50.3 dB	45.8 dB	42.8 dB	25 dB	27 dB	100 ± 15 Ohm
31.25 MHz	10.2 dB/100m	59.9 dB	57.9 dB	49.7 dB	47.7 dB	43.9 dB	40.9 dB	25 dB	27 dB	100 ± 15 Ohm
62.5 MHz	14.7 dB/100m	55.4 dB	53.4 dB	40.7 dB	38.7 dB	37.9 dB	34.9 dB	25 dB	27 dB	100 ± 15 Ohm
100 MHz	18.9 dB/100m	52.3 dB	50.3 dB	33.4 dB	31.4 dB	33.8 dB	30.8 dB	25 dB	27 dB	100 ± 15 Ohm
155 MHz	23.9 dB/100m	49.5 dB	47.5 dB	25.5 dB	23.5 dB	30 dB	27 dB	22.8 dB	24.7 dB	100 ± 15 Ohm
200 MHz	27.5 dB/100m	47.8 dB	45.8 dB	20.3 dB	18.3 dB	27.8 dB	24.8 dB	21.7 dB	23.4 dB	100 ± 15 Ohm
250 MHz	31.2 dB/100m	46.3 dB	44.3 dB	15.2 dB	13.2 dB	25.8 dB	22.8 dB	20.5 dB	22.2 dB	100 ± 20 Ohm
300 MHz	34.5 dB/100m	43.2 dB	41.2 dB	10.6 dB	8.6 dB	24.3 dB	21.3 dB	20.2 dB	21.2 dB	100 ± 20 Ohm
310 MHz	35.2 dB/100m	42.9 dB	40.9 dB	9.8 dB	7.8 dB	24 dB	21 dB	20.1 dB	21.1 dB	100 ± 20 Ohm
350 MHz	37.7 dB/100m	42.2 dB	40.2 dB	6.5 dB	4.5 dB	22.9 dB	19.9 dB	19.8 dB	20.4 dB	100 ± 22 Ohm
400 MHz	40.6 dB/100m	41.3 dB	39.3 dB	2.6 dB	0.6 dB	21.8 dB	18.8 dB	19.5 dB	19.7 dB	100 ± 22 Ohm
450 MHz	43.5 dB/100m	40.5 dB	38.5 dB	2.1 dB	0.1 dB	20.7 dB	17.7 dB	18.9 dB	19.1 dB	100 ± 22 Ohm
460 MHz	44 dB/100m	40.4 dB	38.4 dB	0 dB	0 dB	20.5 dB	17.5 dB	18.8 dB	19 dB	100 ± 22 Ohm
500 MHz	46.2 dB/100m	39.8 dB	37.8 dB			19.8 dB	16.8 dB	18.4 dB	18.5 dB	100 ± 22 Ohm
550 MHz	48.8 dB/100m	39.2 dB	37.2 dB			19 dB	16 dB	18 dB	18 dB	100 ± 22 Ohm
600 MHz	51.4 dB/100m	38.6 dB	36.6 dB			18.2 dB	15.2 dB	17.6 dB	17.6 dB	100 ± 22 Ohm

Voltage

UL Voltage Rating
300V RMS

Temperature Range

Installation Temp Range:	-25°C To +75°C
UL Temp Rating:	60°C
Storage Temp Range:	-40°C To +75°C
Operating Temp Range:	-40°C To +75°C

Mechanical Characteristics

Bulk Cable Weight:	33.5 lbs/1000ft
Max Recommended Pulling Tension:	45 lbs
Min Bend Radius/Minor Axis:	0.25 in

Standards

NEC/(UL) Specification:	CMR, UL444
CEC/C(UL) Specification:	CMR
UL AWM Style:	UL Style 444 (300 V 75°C)
ISO/IEC Compliance:	ISO/IEC 11801 ed 2.1 (2008) Class E
CPR Euroclass:	Eca
Data Category:	Category 6
Telecommunications Standards:	Category 6 - TIA 568.C.2
Other Specification:	NEMA WC-63.1 Category 6,

Applicable Environmental and Other Programs

EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

Suitability

Suitability - Oil Resistance:	Yes
Suitability - Sunlight Resistance:	Yes

Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT4
UL Flammability:	UL1666 Riser

Part Number

Plenum (Y/N):	No
---------------	----

Variants

Item #	Color	Footnote
7927A 0101000	BLACK	C
7927A 0102000	BLACK	C
7927A 0105000	BLACK	C

Footnote:	C - CRATE REEL PUT-UP.
Patent:	http://www.belden.com/p

Product Notes

Notes:	Third party verified to TIA/EIA-568-B.2, Category 6. Operating temperature subject to length de-rating. Cable passes -40C Cold Bend per UL 1581.
--------	--

© 2018 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.