

Part Number: 89292



Analog Video, RG11, #14 Solid BC, Foil + 65% TC Braid, FEP Jacket, CMP

## **Product Description**

14 AWG solid .064" bare copper conductor, plenum, foam FEP insulation, Duofoil®; tinned copper braid shield (65% coverage), FEP jacket.

# **Technical Specifications**

#### **Product Overview**

Environmental Space:	Indoor - Plenum	
Physical Characteristics (Overall)		

#### Conductor

AWG	Stranding	Material	Nominal Diameter	No. of Coax
14	Solid	BC - Bare Copper	0.064 in	1
Conductor Count:		1		
AWG Size:		14		

#### Insulation

Material	Nominal Diameter
FFEP - Foam Fluorinated Ethylene Propylene	0.274 in

# Outer Shield Material

Type	Layer	Material	Material Trade Name	Coverage [%]
Tape	1	Aluminum Foil-Polyester Tape-Aluminum Foil	Duofoil®	100 %
Braid	2	TC - Tinned Copper		65 %

#### **Outer Jacket Material**

Material	Material Trade Name	Nominal Diameter
FEP - Fluorinated Ethylene Propylene	Teflon®	0.346 in

#### **Electrical Characteristics**

#### Conductor DCR

Nominal Conductor DCR	Nominal Conductor DCR Conductor Resistance	Nominal Outer Shield DCR	Outer Conductor DCR
2.5 Ohm/1000ft	2.5 Ohm/1000ft	3 Ohm/1000ft	3 Ohm/1000ft

### Capacitance

Nom. Capacitance Conductor to Shield 16.2 pF/ft

#### Inductance

Nominal Inductance

### Impedance

Nominal Characteristic Impedance
75 Ohm

## High Frequency (Nominal/Typical)

Frequency [MHz]	Nom. Insertion Loss	Nom. Structural Return Loss (SRL)
1 MHz	0.2 dB/100ft	23 dB

450 MHz	0.4 dB/100ft	
5 MHz	1 dB/100ft	
100 MHz	1.5 dB/100ft	
200 MHz	2.2 dB/100ft	
400 MHz	3.3 dB/100ft	
700 MHz	4.5 dB/100ft	
900 MHz	5.2 dB/100ft	
1000 MHz	5.5 dB/100ft	

# Delay

Nominal Delay	Nominal Velocity of Propagation (VP) [%]
1.22 ns/ft	83 %

### Voltage

UL Voltage Rating 300 V RMS

# **Temperature Range**

Non-UL Temp Rating:	200°C
Operating Temp Range:	-70°C To +200°C

# **Mechanical Characteristics**

Bulk Cable Weight:	73 lbs/1000ft
Max Recommended Pulling Tension:	97 lbs
Min Bend Radius/Minor Axis:	4 in

# **Standards**

NEC/(UL) Specification:	CMP, CATVP
CEC/C(UL) Specification:	CMP
RG Type:	RG-11/U Type

# **Applicable Environmental and Other Programs**

EU Directive 2000/53/EC (ELV):	Yes
EU Directive 2003/11/EC (BFR):	Yes
EU Directive 2011/65/EU (ROHS II):	Yes
EU Directive 2012/19/EU (WEEE):	Yes
EU Directive 2015/863/EU:	Yes
EU Directive Compliance:	EU Directive 2003/11/EC (BFR)
EU CE Mark:	Yes
EU RoHS Compliance Date (yyyy-mm-dd):	2005-04-01
CA Prop 65 (CJ for Wire & Cable):	Yes
MII Order #39 (China RoHS):	Yes

# Suitability

Suitability - Indoor:	Yes

# Flammability, LS0H, Toxicity Testing

C(UL) Flammability:	FT6
UL Flammability:	NFPA 262

### **Part Number**

Plenum (Y/N):	Yes
Non-Plenum Number:	9292
Footnote:	C - CRATE REEL PUT-UP.

# **Product Notes**

Notes:	Teflon® is a registered trademark of E. I. duPont de Nemours and Co. used under license by Belden, Inc.
--------	---

© 2018 Belden, Inc

### All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with EU RoHS(Directive 2002/95/EC, 27-Jan-2003). Material manufactured prior to the compliance date may be instock at Belden facilities and in our Distributor's inventory. The information provided in this Product Disclosure, and the identification of materials listed as reportable or restricted within the Product Disclosure, is correct to the best of Belden's knowledge, information, and belief at the date of its publication. The information provided in this Product Disclosure is designed only as a general guide for the safe handling, storage, and any other operation of the product tistelf or the one that it becomes a part of. This Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Belden declares this product to be in compliance with EU LVD (Low Voltage Directive 73/23/EEC), as amended by directive 93/68/EEC.