



Main

| | |
|---|---|
| Range | TeSys |
| Product name | TeSys D |
| Product or component type | Contactor |
| Device short name | LC1D |
| Contactor application | Resistive load |
| Utilisation category | AC-1 |
| Poles description | 4P |
| Pole contact composition | 2 NO + 2 NC |
| [Ue] rated operational voltage | <= 300 V DC for power circuit <= 690 V AC 25...400 Hz for power circuit |
| [Ie] rated operational current | 40 A (<= 60 °C) at <= 440 V AC AC-1 for power circuit |
| Control circuit type | AC 50/60 Hz |
| [Uc] control circuit voltage | 110 V AC 50/60 Hz |
| Auxiliary contact composition | 1 NO + 1 NC |
| [Uimp] rated impulse withstand voltage | 6 kV conforming to IEC 60947 |
| Overvoltage category | III |
| [Ith] conventional free air thermal current | 40 A at <= 60 °C for power circuit 10 A at <= 60 °C for signalling circuit |
| Irms rated making capacity | 450 A at 440 V for power circuit conforming to IEC 60947 140 A AC for signalling circuit conforming to IEC 60947-5-1 250 A DC for signalling circuit conforming to IEC 60947-5-1 |
| Rated breaking capacity | 450 A at 440 V for power circuit conforming to IEC 60947 |
| [Icw] rated short-time withstand current | 120 A <= 40 °C 1 min power circuit 240 A <= 40 °C 10 s power circuit 380 A <= 40 °C 1 s power circuit 50 A <= 40 °C 10 min power circuit 100 A 1 s signalling circuit 120 A 500 ms signalling circuit 140 A 100 ms signalling circuit |
| Associated fuse rating | 40 A gG at <= 690 V coordination type 2 for power circuit 63 A gG at <= 690 V coordination type 1 for power circuit 10 A gG for signalling circuit conforming to IEC 60947-5-1 |
| Average impedance | 2 mOhm at 50 Hz - Ith 40 A for power circuit |
| [Ui] rated insulation voltage | 600 V for power circuit certifications CSA 600 V for power circuit certifications UL 690 V for power circuit conforming to IEC 60947-4-1 |

Disclaimer: This documentation is not intended as a substitute for and is not to be used for determining suitability or reliability of these products for specific user applications

690 V for signalling circuit conforming to IEC 60947-1
 600 V for signalling circuit certifications CSA
 600 V for signalling circuit certifications UL

| | |
|----------------------------|--|
| Electrical durability | 1.4 Mcycles 40 A AC-1 at $U_e \leq 440$ V |
| Power dissipation per pole | 3.2 W AC-1 |
| Protective cover | With |
| Mounting support | Plate Rail |
| Standards | CSA C22.2 No 14 EN 60947-4-1 EN 60947-5-1 IEC 60947-4-1 IEC 60947-5-1 UL 508 |
| Product certifications | DNV CCC BV LROS (Lloyds register of shipping) UL GOST RINA CSA GL |
| Connections - terminals | Control circuit : screw clamp terminals 2 cable(s) 1...2.5 mm ² - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: flexible - without cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: flexible - with cable end Control circuit : screw clamp terminals 1 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Control circuit : screw clamp terminals 2 cable(s) 1...4 mm ² - cable stiffness: solid - without cable end Power circuit : connector 1 cable(s) 2.5...10 mm ² - cable stiffness: flexible - without cable end Power circuit : connector 2 cable(s) 2.5...10 mm ² - cable stiffness: flexible - without cable end Power circuit : connector 1 cable(s) 2.5...10 mm ² - cable stiffness: flexible - with cable end Power circuit : connector 2 cable(s) 2.5...10 mm ² - cable stiffness: flexible - with cable end Power circuit : connector 1 cable(s) 2.5...16 mm ² - cable stiffness: solid - without cable end Power circuit : connector 2 cable(s) 2.5...16 mm ² - cable stiffness: solid - without cable end |
| Tightening torque | Control circuit : 1.7 N.m - on screw clamp terminals - with screwdriver flat \varnothing 6 mm Control circuit : 1.7 N.m - on screw clamp terminals - with screwdriver Philips No 2 Power circuit : 1.8 N.m - on connector - with screwdriver flat \varnothing 6 mm Power circuit : 1.8 N.m - on connector - with screwdriver Philips No 2 |
| Operating time | 4...19 ms opening 12...22 ms closing |
| Safety reliability level | B10d = 1369863 cycles contactor with nominal load conforming to EN/ISO 13849-1 B10d = 20000000 cycles contactor with mechanical load conforming to EN/ISO 13849-1 |
| Mechanical durability | 15 Mcycles |
| Operating rate | 3600 cyc/h at ≤ 60 °C |

Complementary

| | |
|---------------------------------|---|
| Coil technology | Without built-in suppressor module |
| Control circuit voltage limits | 0.3...0.6 U_c drop-out at 60 °C, AC 50/60 Hz 0.8...1.1 U_c operational at 60 °C, AC 50 Hz 0.85...1.1 U_c operational at 60 °C, AC 60 Hz |
| Inrush power in VA | 70 VA at 20 °C ($\cos \phi$ 0.75) 60 Hz 70 VA at 20 °C ($\cos \phi$ 0.75) 50 Hz |
| Hold-in power consumption in VA | 7.5 VA at 20 °C ($\cos \phi$ 0.3) 60 Hz 7 VA at 20 °C ($\cos \phi$ 0.3) 50 Hz |
| Heat dissipation | 2...3 W at 50/60 Hz |
| Auxiliary contacts type | Type mechanically linked (1 NO + 1 NC) conforming to IEC 60947-5-1 Type mirror contact (1 NC) conforming to IEC 60947-4-1 |
| Signalling circuit frequency | 25...400 Hz |
| Minimum switching current | 5 mA for signalling circuit |
| Minimum switching voltage | 17 V for signalling circuit |
| Non-overlap time | 1.5 ms on energisation between NC and NO contact |

1.5 ms on de-energisation between NC and NO contact

| | |
|-----------------------|----------------------------------|
| Insulation resistance | > 10 MOhm for signalling circuit |
|-----------------------|----------------------------------|

Environment

| | |
|-------------------------|---|
| IP degree of protection | IP20 front face conforming to IEC 60529 |
|-------------------------|---|

| | |
|----------------------|---------------------------------|
| Protective treatment | TH conforming to IEC 60068-2-30 |
|----------------------|---------------------------------|

| | |
|------------------|---|
| Pollution degree | 3 |
|------------------|---|

| | |
|---------------------------------------|------------|
| Ambient air temperature for operation | -5...60 °C |
|---------------------------------------|------------|

| | |
|-------------------------------------|-------------|
| Ambient air temperature for storage | -60...80 °C |
|-------------------------------------|-------------|

| | |
|---|-------------------|
| Permissible ambient air temperature around the device | -40...70 °C at Uc |
|---|-------------------|

| | |
|--------------------|--|
| Operating altitude | 3000 m without derating in temperature |
|--------------------|--|

| | |
|-----------------|------------------------------------|
| Fire resistance | 850 °C conforming to IEC 60695-2-1 |
|-----------------|------------------------------------|

| | |
|------------------|------------------------|
| Flame retardance | V1 conforming to UL 94 |
|------------------|------------------------|

| | |
|-----------------------|---|
| Mechanical robustness | Vibrations contactor open 2 Gn, 5...300 Hz Vibrations contactor closed 4 Gn, 5...300 Hz Shocks contactor closed 15 Gn for 11 ms Shocks contactor open 8 Gn for 11 ms |
|-----------------------|---|

| | |
|--------|--------|
| Height | 105 mm |
|--------|--------|

| | |
|-------|-------|
| Width | 45 mm |
|-------|-------|

| | |
|-------|-------|
| Depth | 99 mm |
|-------|-------|

| | |
|----------------|----------|
| Product weight | 0.425 kg |
|----------------|----------|

Contractual warranty

| | |
|-----------------|-----------|
| Warranty period | 18 months |
|-----------------|-----------|
